



Flexitest switches FT-1 & FT-14

Selection guide

Table of contents

Table 1. FT-1 switch selection guide	4-12
Table 2. FT-1 switch selection by style	13-18
Table 3. FT-14 switch selection guide	19-20
Notes	21
Additional notes	22-23

The Flexitest switches FT-1 & FT-14 selection guide includes the most frequently used configurations. For more options, please visit us at www.ft1switch.com.

The FT-1 Configurator is a web based tool to help build any complete FT switch arrangement, select options, view schematic details and get style number information. We strongly recommend the use of our web site for quick, easy and user friendly configuration of the Flexitest switches.




Table 1. FT-1 switch selection guide

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
		A	B	C	D	E	F	G	H	I	J		
1 Pole		A	B	C	D	E	F	G	H	I	J		
1	0	P	.	.	.	.	.	.	.	.	.	774B542G09	129A062G10
2 Pole		A	B	C	D	E	F	G	H	I	J		
2	0	.	.	.	.	.	.	.	P	.	P	291B954G15	129A062G10
2	0	.	.	.	P	.	.	P	.	.	.	129A534G01	129A062G10
2	0	P	P	.	.	.	.	.	.	.	.	291B954G13	129A062G10
2	0	T	.	.	.	.	.	.	.	.	T	291B954G14	129A062G10
2	0	T	O	.	.	.	.	.	.	.	.	9688A46G01	129A062G10
2	0	T	T	.	.	.	.	.	.	.	.	291B954G16	129A062G10
2	0	Z	Z	.	.	.	.	.	.	.	.	9676A38G01	129A062G10
0	2	.	.	.	.	.	.	.	C	-	C	291B954G12	129A062G01
0	2	.	.	.	.	C	-	C	.	.	.	129A531G01	129A062G08
0	2	.	C	-	C	.	.	.	.	.	.	498A026G01	129A062G07
0	2	C	-	C	.	.	.	.	.	.	.	9689A74G01	129A062G07
3 Pole		A	B	C	D	E	F	G	H	I	J		
3	0	.	.	.	.	.	.	.	P	P	P	716B871G11	129A062G10
3	0	.	.	.	P	P	P	.	.	.	.	716B871G09	129A062G10
3	0	.	.	.	T	T	T	.	.	.	.	9689A75G01	129A062G10
3	0	.	.	.	Z	Z	Z	.	.	.	.	9688A63G01	129A062G10
3	0	P	.	.	.	P	.	.	.	.	P	716B871G12	129A062G10
3	0	T	Y	O	.	.	.	.	.	.	.	991A939G01	129A062G10
1	2	C	-	C	.	.	.	.	.	.	T	9663A78G01	<1>
0	3	.	.	.	C	C	C	.	.	.	.	716B871G10	<1>
4 Pole		A	B	C	D	E	F	G	H	I	J		
4	0	.	.	.	T	P	T	P	.	.	.	9676A26G01	129A062G10
4	0	.	.	.	T	T	T	P	.	.	.	9676A27G01	129A062G10
4	0	.	.	P	P	P	P	.	.	.	.	129A524G01	129A062G10
4	0	.	.	T	.	T	.	T	.	T	.	291B956G31	129A062G10
4	0	.	.	T	T	T	T	.	.	.	.	1586C39G01	129A062G10
4	0	.	.	T	T	T	T	.	.	.	.	291B956G32	129A062G10
4	0	.	.	Z	Z	Z	Z	.	.	.	.	9689A80G01	129A062G10
4	0	.	P	.	P	.	P	.	P	.	.	9688A64G01	129A062G10
4	0	P	.	.	.	.	.	.	P	P	P	129A506G01	129A062G10
4	0	P	.	.	P	.	.	P	.	.	P	291B956G24	129A062G10
4	0	P	.	.	P	P	P	.	.	.	.	291B956G25	129A062G10
4	0	P	.	.	T	.	.	Y	.	.	Z	9647A17G01	129A062G10
4	0	P	P	.	.	.	.	.	.	P	P	129A538G01	129A062G10
4	0	P	P	P	.	.	.	.	.	.	P	498A022G01	129A062G10
4	0	P	P	P	.	.	.	.	.	.	T	9663A80G01	129A062G10
4	0	P	P	P	P	.	.	.	.	.	.	9672A73G01	129A062G10
4	0	T	.	.	.	.	.	.	P	P	T	763A166G01	129A062G10
4	0	T	.	.	.	.	.	.	T	T	T	498A012G01	129A062G10
4	0	T	.	T	.	.	.	.	T	.	T	862A584G01	129A062G10
4	0	T	T	.	.	.	.	.	P	P	.	991A932G01	129A062G10
4	0	T	T	T	.	.	.	.	.	.	T	1586C39G02	129A062G10
4	0	T	T	T	T	.	.	.	.	.	.	9688A79G01	129A062G10
5 Pole		A	B	C	D	E	F	G	H	I	J		
5	0	P	P	.	.	.	.	.	P	P	P	129A505G01	129A062G10
5	0	P	P	P	P	P	.	.	.	.	.	291B957G15	129A062G10
5	0	T	T	.	.	.	.	.	T	T	T	9676A37G01	129A062G10
5	0	T	Y	Z	W	P	.	.	.	.	.	9688A55G01	129A062G10
3	2	P	C	-	C	P	.	.	.	.	P	129A508G01	129A062G07
3	2	P	P	.	.	.	.	.	C	-	C	129A533G01	129A062G01
3	2	P	P	.	.	.	.	.	C	-	C	9666A95G01	129A062G01
3	2	P	P	.	.	C	-	C	.	.	P	291B957G17	<1>
3	2	P	P	P	C	-	C	.	.	.	.	291B957G16	<1>
3	2	T	P	.	.	.	.	.	C	-	C	291B957G09	129A062G01
1	4	.	C	C	.	C	.	C	.	P	.	498A002G01	<1>
1	4	C	-	C	-	C	-	C	.	.	.	9689A54G01	<1>
0	5	C	.	C	.	C	.	C	.	C	.	129A555G01	<1>
6 Pole		A	B	C	D	E	F	G	H	I	J		
6	0	.	.	.	P	P	P	P	P	P	P	188A416G01	129A062G10
6	0	P	P	.	.	.	.	.	P	P	P	837A889G01	129A062G10
6	0	P	P	.	.	P	P	.	.	P	P	629A568G01	129A062G10
6	0	P	P	P	.	.	.	.	P	P	P	129A504G01	129A062G10
6	0	P	P	P	P	.	.	.	.	P	P	129A550G01	129A062G10
6	0	P	P	P	P	P	P	.	.	.	.	291B958G25	129A062G10
6	0	P	P	T	.	.	.	.	T	T	T	1586C40G01	129A062G10
6	0	T	T	T	T	.	.	.	.	P	P	9683A81G01	129A062G10
6	0	T	T	T	T	.	.	.	.	T	T	291B958G33	129A062G10
6	0	T	T	T	T	T	T	.	.	.	.	9676A65G01	129A062G10

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
A	B	C	D	E	F	G	H	I	J				
6	0	T	Y	O	.	.	.	O	Y	T		9688A40G01	129A062G10
6	0	W	W	.	.	P	P	.	W	W		9688A04G01	129A062G10
6	0	Y	Y	Y	Y	.	.	.	Y	Y		9669A31G01	129A062G10
6	0	Z	Z	Z	P	P	.	.	.	P		9666A39G01	129A062G10
4	2	P	.	.	.	.	P	P	C	C	P	129A509G01	129A062G01
4	2	P	P	P	P	R	R	.	.	.		9667A02G01	<1>
4	2	T	T	.	.	.	P	P	.	C	C	9672A03G01	<1>
3	3	P	P	.	.	.	.	C	C	C	P	291B958G24	<1>
3	3	P	P	.	.	.	.	C	C	C	P	129A543G01	129A062G02
3	3	P	P	P	.	.	.	C	C	C	.	9676A19G01	<1>
2	4	.	.	.	C	C	C	C	P	P	.	291B958G30	129A062G12
2	4	P	.	.	.	.	C	C	C	C	P	129A537G01	129A062G02
2	4	P	.	.	.	.	P	C	C	C	C	291B958G31	<1>
2	4	P	.	.	C	C	C	C	.	.	P	291B958G27	<1>
0	6	.	.	.	.	C	C	C	C	C	C	9672A72G01	<1>
0	6	.	.	.	.	R	R	7	7	8	8	9688A43G01	<1>
0	6	.	.	.	.	R	R	8	8	7	7	9688A30G01	<1>
0	6	.	.	.	8	8	8	8	8	8	8	9689A78G01	292B319G23
0	6	.	.	.	C	C	C	C	C	C	.	188A454G01	<1>
0	6	.	.	.	C	A	C	A	C	A	.	291B958G26	<1>
0	6	.	.	.	C	A	C	A	C	C	.	291B958G29	<1>
0	6	.	.	.	C	B	C	B	C	B	.	498A017G01	<1>
0	6	.	.	.	C	C	C	C	C	C	.	129A516G01	292B319G23
0	6	.	.	.	R	R	R	R	R	R	.	291B958G28	292B319G23
0	6	.	.	C	C	C	C	C	C	C	.	129A523G01	<1>
0	6	.	6	6	.	7	7	.	9	9	.	9666A83G01	<1>
0	6	.	C	C	.	C	C	.	C	C	.	498A014G01	<1>
0	6	.	C	C	C	C	C	C	C	.	.	9683A76G01	<1>
0	6	C	.	C	.	C	.	.	C	C	C	188A304G01	<1>
0	6	C	C	.	.	C	C	.	.	C	C	9689A23G01	<1>
0	6	C	C	C	C	C	C	.	.	.	.	9660A97G01	<1>
7 Pole		A	B	C	D	E	F	G	H	I	J		
7	0	.	.	.	T	T	T	T	T	T	T	9688A99G01	129A062G10
7	0	.	P	P	P	P	P	P	P	.	.	129A526G01	129A062G10
7	0	P	.	.	P	P	P	.	P	P	P	129A503G01	129A062G10
7	0	P	.	.	P	P	P	P	P	.	P	291B959G19	129A062G10
7	0	P	P	P	.	.	.	P	P	P	P	129A547G01	129A062G10
7	0	P	P	P	.	.	.	P	P	P	P	291B959G30	129A062G10
7	0	P	P	P	P	.	.	P	P	P	.	498A013G01	129A062G10
7	0	P	P	P	P	P	P	.	.	.	T	9663A79G01	129A062G10
7	0	P	P	P	P	P	P	P	.	.	.	291B959G28	129A062G10
7	0	T	.	.	P	P	P	.	P	P	T	763A168G01	129A062G10
7	0	T	T	P	.	.	.	P	P	P	P	291B959G33	129A062G10
5	2	P	C	C	P	.	.	.	P	P	P	188A261G01	129A062G07
5	2	P	P	.	.	.	C	C	P	P	P	129A510G01	129A062G08
5	2	P	P	P	P	P	.	.	.	C	C	291B959G27	<1>
5	2	P	P	P	P	P	.	.	C	C	.	291B959G18	129A062G01
5	2	T	P	.	.	.	P	P	C	C	T	188A622G01	129A062G01
5	2	T	T	.	.	.	R	R	T	T	T	9667A17G01	129A062G08
4	3	P	P	C	.	C	.	C	.	P	P	188A477G01	292B319G24
3	4	P	C	C	.	C	.	C	.	P	P	188A618G01	<1>
3	4	P	C	C	.	P	.	C	C	.	P	9688A83G01	<1>
3	4	P	P	.	.	.	C	C	C	C	P	129A511G01	129A062G02
3	4	P	P	P	.	.	C	C	C	C	.	498A008G01	129A062G02

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
A	B	C	D	E	F	G	H	I	J				
3	4	T	C	C	T	C	C	T	.	.	.	291B959G26	<1>
3	4	T	T	T	.	.	C	C	C	C	.	291B959G32	<1>
3	4	T	T	T	.	.	C	C	C	C	.	291B959G20	129A062G02
3	4	T	T	T	.	C	C	.	.	C	C	9676A79G01	<1>
2	5	C	C	C	C	C	T	T	.	.	.	9682A43G01	<1>
1	6	.	.	.	C	C	C	C	C	C	T	498A003G01	292B319G23
1	6	C	C	C	C	C	C	C	.	.	T	9663A77G01	<1>
1	6	P	C	C	C	B	C	B	.	.	.	129A540G01	<1>
1	6	T	.	.	.	R	R	8	8	7	7	991A936G01	<1>
0	7	.	.	C	C	C	C	C	C	C	C	291B959G29	292B319G22
0	7	C	C	C	C	C	C	C	C	.	.	9676A24G01	<1>
8 Pole		A	B	C	D	E	F	G	H	I	J		
8	0	.	P	P	P	P	P	P	P	P	.	291B960G37	129A062G10
8	0	O	O	O	O	O	O	O	O	O	.	9689A95G01	129A062G10
8	0	P	.	.	P	P	P	P	P	P	P	129A549G01	129A062G10
8	0	P	P	.	P	P	.	P	P	P	P	9689A22G01	129A062G10
8	0	P	P	P	.	.	P	P	P	P	P	719B591G09	129A062G10
8	0	P	P	P	.	P	P	.	P	P	P	291B960G39	129A062G10
8	0	P	P	P	P	.	.	P	P	P	P	129A502G01	129A062G10
8	0	P	P	P	P	.	.	P	P	P	T	129A536G01	129A062G10
8	0	P	P	P	P	P	.	.	P	P	P	129A546G01	129A062G10
8	0	P	P	P	P	P	.	.	P	T	T	719B591G14	129A062G10
8	0	P	P	P	P	P	P	.	.	T	T	9683A80G01	129A062G10
8	0	P	P	P	P	P	P	P	P	.	.	719B591G10	129A062G10
8	0	T	T	.	.	Z	Z	Z	Z	Z	Z	9689A90G01	129A062G10
8	0	T	T	T	.	T	.	O	O	G	G	9689A76G01	129A062G10
8	0	T	T	T	T	.	.	T	T	T	T	9683A10G01	129A062G10
8	0	T	T	T	T	T	.	.	T	T	T	719B591G12	129A062G10
8	0	T	T	T	T	T	T	.	.	T	T	991A937G01	129A062G10
6	2	O	O	C	C	.	.	Z	Z	Z	Z	9683A71G01	<1>
6	2	P	P	P	.	.	C	C	P	P	P	291B960G26	129A062G08
6	2	P	P	P	P	P	.	.	C	C	P	188A632G01	129A062G01
6	2	P	P	P	P	P	P	.	.	C	C	291B960G36	<1>
6	2	T	.	.	P	P	P	P	C	C	T	763A167G01	129A062G01
6	2	W	W	W	W	W	W	.	.	C	C	9689A16G01	<1>
4	4	.	.	P	P	P	C	C	C	C	P	629A315G01	129A062G02
4	4	C	C	C	C	.	.	P	P	P	P	719B591G13	<1>
4	4	C	C	C	C	.	.	P	P	P	P	719B591G11	<1>
4	4	C	C	C	C	W	W	W	W	.	.	9669A32G01	<1>
4	4	P	C	C	P	.	.	P	C	C	P	129A512G01	129A062G06
4	4	P	P	.	C	C	C	C	.	P	P	498A016G01	<1>
4	4	P	P	.	C	C	C	C	.	P	P	129A530G01	129A062G12
4	4	P	P	P	P	.	C	C	C	C	.	129A544G01	129A062G02
3	5	T	P	.	.	C	C	C	C	C	T	291B960G27	292B319G23
2	6	.	C	C	C	C	C	C	C	.	P	9667A21G01	<1>
2	6	.	C	C	C	C	C	C	C	.	P	129A521G01	129A062G09
2	6	.	C	C	C	C	C	C	C	.	T	9683A22G01	129A062G09
2	6	.	C	C	C	C	C	C	C	P	P	129A525G01	129A062G09
2	6	C	B	C	B	C	B	.	.	P	P	291B960G38	<1>
2	6	C	C	C	C	C	C	.	.	T	T	991A938G01	<1>
2	6	T	T	.	.	C	C	C	C	C	C	9668A69G01	<1>
2	6	Z	Z	.	.	C	C	C	C	C	C	9688A65G01	<1>
1	7	C	.	.	C	B	C	B	C	B	P	498A018G01	<1>
1	7	P	.	C	C	C	C	C	C	C	.	498A019G01	292B319G22

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug						
		A	B	C	D	E	F	G	H	I	J								
0	8	.	C	C	C	C	C	C	C	C	.	498A004G01	<1>						
0	8	.	C	-	C	-	C	-	C	-	C	129A517G01	292B319G22						
0	8	.	C	-	C	-	C	-	B	.	C	498A029G01	<1>						
0	8	.	C	-	C	-	C	-	B	C	-	291B960G20	<1>						
0	8	.	C	-	C	-	C	-	C	C	-	291B960G33	<1>						
0	8	.	R	-	R	R	-	R	-	R	-	9660A84G01	292B319G22						
0	8	5	-	5	.	.	R	-	R	7	-	7	8	-	8	9688A42G01	<1>		
0	8	5	-	5	-	5	-	A	.	.	5	-	5	-	5	-	A	9689A27G01	<1>
0	8	6	-	6	R	-	R	5	-	5	.	.	8	-	8	9666A78G01	<1>		
0	8	C	C	C	C	.	.	C	C	C	C	188A229G01	<1>						
0	8	C	-	C	.	.	C	-	C	C	-	C	9672A10G01	<1>					
0	8	C	-	C	C	-	C	C	-	C	.	.	C	1586C41G01	<1>				
0	8	C	-	C	C	-	C	C	-	C	C	-	.	9689A20G01	<1>				
0	8	C	-	C	-	C	-	A	.	.	C	-	C	-	A	9683A93G01	<1>		
0	8	C	-	C	-	C	-	A	C	-	C	-	C	-	B	.	837A099G01	<1>	
0	8	C	-	C	-	C	-	B	.	.	C	-	C	-	C	-	B	498A025G01	<1>
0	8	C	-	C	-	C	-	C	.	.	C	-	C	-	C	-	C	9666A85G01	<1>
0	8	C	-	C	-	C	-	C	C	-	C	-	C	-	B	.	837A098G01	<1>	
0	8	D	D	D	C	-	C	-	C	-	C	-	S	.	.	9688A70G01	<1>		
9 Pole		A	B	C	D	E	F	G	H	I	J								
9	0	P	P	.	P	P	P	P	P	P	P	129A548G01	129A062G10						
9	0	P	P	P	P	.	P	P	P	P	P	129A551G01	129A062G10						
9	0	P	P	P	P	.	T	T	T	T	T	9682A44G01	129A062G10						
9	0	P	P	P	P	P	P	P	P	P	.	9689A21G01	129A062G10						
9	0	T	T	T	T	T	T	T	.	O	T	991A940G01	129A062G10						
9	0	T	T	T	T	T	T	T	T	.	T	9688A45G01	129A062G10						
6	3	P	P	P	C	C	C	P	P	P	.	291B961G23	<1>						
6	3	P	P	P	P	P	.	C	C	C	P	291B961G30	<1>						
6	3	P	P	P	P	P	.	C	C	-	C	P	129A552G01	129A062G02					
6	3	P	P	P	P	P	.	C	-	C	C	P	629A483G01	<1>					
5	4	P	P	P	P	.	C	-	C	C	-	C	P	188A633G01	129A062G02				
5	4	P	P	P	P	P	.	C	-	C	C	-	C	291B961G22	<1>				
5	4	P	P	P	P	P	C	C	C	C	.	291B961G28	<1>						
5	4	P	P	P	P	P	C	-	C	C	-	C	129A545G01	129A062G02					
4	5	P	P	P	P	.	C	C	-	C	-	C	-	B	498A028G01	<1>			
4	5	P	P	P	P	.	C	-	C	-	C	-	E	9689A10G01	<1>				
3	6	.	T	C	-	C	T	C	-	C	T	C	-	C	9663A34G01	<1>			
3	6	P	C	-	C	P	C	-	C	P	C	-	C	.	861A551G01	<1>			
3	6	P	P	.	C	-	C	C	-	C	C	-	C	P	129A515G01	292B319G23			
3	6	P	P	P	.	C	-	C	C	-	C	-	C	-	B	498A024G01	<1>		
3	6	P	P	P	C	-	C	C	-	C	.	C	C	291B961G27	<1>				
3	6	P	P	P	C	-	C	C	-	C	C	-	C	.	291B961G29	292B319G23			
3	6	T	T	.	C	-	C	C	-	C	C	-	C	T	9663A74G01	292B319G23			
3	6	T	T	O	.	R	-	R	8	-	8	7	-	7	9689A56G01	<1>			
3	6	T	T	T	.	R	-	R	8	-	8	7	-	7	9689A57G01	<1>			
2	7	P	P	.	C	-	B	C	-	B	C	-	B	S	291B961G26	<1>			
1	8	.	C	-	C	C	-	C	C	-	C	C	-	C	T	498A009G01	292B319G22		
1	8	T	.	C	-	C	C	-	C	C	-	C	C	-	C	9668A70G01	<1>		
0	9	.	C	C	-	B	C	C	-	B	C	C	-	B	498A023G01	<1>			
0	9	C	C	-	C	-	C	C	-	C	C	-	C	.	498A021G01	<1>			
0	9	C	-	C	C	-	C	C	-	C	C	.	C	-	C	9676A25G01	<1>		
10 Pole		A	B	C	D	E	F	G	H	I	J								
10	0	G	G	G	G	G	G	G	G	G	G	9688A58G01	129A062G10						
10	0	G	G	G	G	G	G	G	G	Y	Y	9689A62G01	129A062G10						

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
10	0	G	G	G	G	G	G	T	G	T	T	9689A37G01	129A062G10
10	0	G	G	G	G	G	G	T	T	T	T	9688A57G01	129A062G10
10	0	G	G	G	G	G	O	O	O	O	O	9666A73G01	129A062G10
10	0	G	G	G	G	G	Y	Y	Y	Y	Y	9688A26G01	129A062G10
10	0	G	G	G	G	G	Z	Z	Z	Z	Z	9683A88G01	129A062G10
10	0	G	G	G	G	P	P	T	T	T	T	9688A56G01	129A062G10
10	0	G	G	G	G	Y	Y	Y	T	T	T	991A623G01	129A062G10
10	0	G	G	G	G	Y	Y	Y	Y	Y	Y	9683A69G01	129A062G10
10	0	G	G	Y	Y	Y	Y	Y	Y	Y	Y	9682A77G01	129A062G10
10	0	G	O	O	O	O	O	O	O	O	O	9682A57G01	129A062G10
10	0	G	T	T	G	T	T	T	T	T	T	9689A65G01	129A062G10
10	0	G	T	T	T	T	T	T	T	G	T	9682A42G01	129A062G10
10	0	G	T	T	T	T	T	T	T	T	T	9689A59G01	129A062G10
10	0	G	Y	T	T	T	G	T	T	T	T	9689A99G01	129A062G10
10	0	O	G	O	P	P	P	P	P	P	P	9688A13G01	129A062G10
10	0	O	O	O	O	O	O	O	O	O	O	9672A97G01	129A062G10
10	0	O	O	O	O	O	Y	Y	Y	Y	Y	9688A08G01	129A062G10
10	0	O	O	O	O	O	Z	Z	Z	Z	Z	9666A58G01	129A062G10
10	0	O	O	T	T	T	T	P	P	P	P	9683A61G01	129A062G10
10	0	O	W	Z	Z	G	W	Y	Y	W	W	9683A18G01	129A062G10
10	0	P	P	G	Y	T	T	T	T	G	G	9669A37G01	129A062G10
10	0	P	P	P	P	G	T	T	P	P	P	9666A50G01	129A062G10
10	0	P	P	P	P	G	T	T	T	P	P	9666A49G01	129A062G10
10	0	P	P	P	P	O	O	O	O	O	O	9666A62G01	129A062G10
10	0	P	P	P	P	P	P	O	O	T	T	9688A90G01	129A062G10
10	0	P	P	P	P	P	P	P	P	P	O	991A621G01	129A062G10
10	0	P	P	P	P	P	P	P	P	P	P	129A501G01	129A062G10
10	0	P	P	P	P	P	P	P	P	P	T	774B430G19	129A062G10
10	0	P	P	P	P	P	P	P	P	P	W	991A930G01	129A062G10
10	0	P	P	P	P	P	P	P	P	T	P	9676A88G01	129A062G10
10	0	P	P	P	P	P	P	P	P	T	T	1586C42G23	129A062G10
10	0	P	P	P	P	P	P	P	P	Z	Z	9671A94G01	129A062G10
10	0	P	P	P	P	P	P	P	T	T	P	9672A77G01	129A062G10
10	0	P	P	P	P	P	P	P	T	T	T	1586C42G25	129A062G10
10	0	P	P	P	P	P	P	P	W	P	P	9682A83G01	129A062G10
10	0	P	P	P	P	P	P	T	P	P	P	1586C42G29	129A062G10
10	0	P	P	P	P	P	P	T	P	P	T	9676A08G01	129A062G10
10	0	P	P	P	P	P	P	T	P	T	P	9672A75G01	129A062G10
10	0	P	P	P	P	P	P	T	P	T	T	1586C42G30	129A062G10
10	0	P	P	P	P	P	P	T	T	T	P	9672A98G01	129A062G10
10	0	P	P	P	P	P	P	T	T	T	T	9672A71G01	129A062G10
10	0	P	P	P	P	P	P	Z	Z	G	T	9688A59G01	129A062G10
10	0	P	P	P	P	P	P	Z	Z	Z	Z	9671A95G01	129A062G10
10	0	P	P	P	P	P	T	P	T	P	T	9676A97G01	129A062G10
10	0	P	P	P	P	P	T	T	T	T	T	1586C42G24	129A062G10
10	0	P	P	P	P	P	T	T	T	T	T	670B197G21	129A062G10
10	0	P	P	P	P	T	G	T	G	P	P	991A931G01	129A062G10
10	0	P	P	P	P	T	P	P	P	P	P	9688A16G01	129A062G10
10	0	P	P	P	P	T	P	P	P	P	T	9688A96G01	129A062G10
10	0	P	P	P	P	T	P	P	T	P	P	9667A06G01	129A062G10
10	0	P	P	P	P	T	P	T	P	T	P	9682A71G01	129A062G10
10	0	P	P	P	P	T	P	T	T	T	T	1586C42G28	129A062G10
10	0	P	P	P	P	T	T	P	P	P	P	9688A95G01	129A062G10
10	0	P	P	P	P	T	T	T	P	P	P	9676A14G01	129A062G10

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
10	0	P	P	P	P	T	T	T	T	P	P	9688A28G01	129A062G10
10	0	P	P	P	P	T	T	T	T	T	P	9688A15G01	129A062G10
10	0	P	P	P	P	T	T	T	T	T	T	670B197G26	129A062G10
10	0	P	P	P	P	W	W	T	T	T	T	9683A95G01	129A062G10
10	0	P	P	P	T	P	P	P	P	P	P	9689A79G01	129A062G10
10	0	P	P	P	T	T	P	P	T	T	T	9666A61G01	129A062G10
10	0	P	P	P	T	T	T	T	T	T	P	9672A74G01	129A062G10
10	0	P	P	P	T	T	T	T	T	T	T	9689A32G01	129A062G10
10	0	P	P	T	P	P	P	P	P	P	P	9676A90G01	129A062G10
10	0	P	P	T	P	T	P	P	P	P	P	1586C42G15	129A062G10
10	0	P	P	T	T	P	P	P	P	O	O	9682A45G01	129A062G10
10	0	P	P	T	T	P	P	P	P	P	P	9666A80G01	129A062G10
10	0	P	P	T	T	T	P	P	T	T	T	9689A97G01	129A062G10
10	0	P	P	T	T	T	T	P	P	P	P	991A224G01	129A062G10
10	0	P	P	T	T	T	T	P	P	T	T	9652A29G01	129A062G10
10	0	P	P	T	T	T	T	T	P	P	P	9664A98G01	129A062G10
10	0	P	P	T	T	T	T	T	T	P	P	9664A97G01	129A062G10
10	0	P	P	T	T	T	T	T	T	T	T	670B197G24	129A062G10
10	0	P	P	W	W	P	P	P	P	Y	Y	9669A34G01	129A062G10
10	0	P	P	Y	Y	Y	Y	W	W	W	W	9682A76G01	129A062G10
10	0	P	T	P	P	P	P	P	P	P	T	9688A20G01	129A062G10
10	0	P	T	P	P	P	P	P	P	T	T	9688A19G01	129A062G10
10	0	P	T	P	P	T	P	P	T	P	P	9668A27G01	129A062G10
10	0	P	T	P	P	T	T	P	P	T	P	9667A03G01	129A062G10
10	0	P	T	P	T	P	P	T	P	T	P	9670A98G01	129A062G10
10	0	P	T	T	P	P	P	P	P	P	P	9671A69G01	129A062G10
10	0	P	T	T	P	P	P	P	T	T	T	9688A18G01	129A062G10
10	0	P	T	T	T	P	P	T	T	P	P	9676A53G01	129A062G10
10	0	P	T	T	T	T	T	T	T	T	T	9688A17G01	129A062G10
10	0	P	T	W	Z	P	P	T	W	Z	P	9683A97G01	129A062G10
10	0	P	W	T	G	O	Z	T	T	T	T	9688A84G01	129A062G10
10	0	P	Y	P	P	P	P	P	P	P	P	991A229G01	129A062G10
10	0	P	Y	P	Y	P	P	Z	Z	T	T	991A225G01	129A062G10
10	0	P	Y	T	T	T	T	P	P	P	P	991A223G01	129A062G10
10	0	P	Y	T	T	T	T	T	P	P	P	991A228G01	129A062G10
10	0	T	G	T	Z	Z	Z	Z	Z	Z	Z	9688A12G01	129A062G10
10	0	T	O	Y	T	Z	O	O	T	Y	T	9688A44G01	129A062G10
10	0	T	P	P	P	P	P	P	P	P	P	1586C42G31	129A062G10
10	0	T	P	P	P	P	P	P	P	P	T	670B197G36	129A062G10
10	0	T	P	P	P	P	P	P	P	P	W	9664A92G01	129A062G10
10	0	T	P	P	P	P	P	P	P	T	T	9682A59G01	129A062G10
10	0	T	P	P	P	P	T	P	P	P	P	9667A93G01	129A062G10
10	0	T	P	P	P	P	T	T	T	T	P	9682A72G01	129A062G10
10	0	T	P	P	T	P	P	P	P	P	P	9670A35G01	129A062G10
10	0	T	P	P	T	P	P	P	P	T	T	9682A73G01	129A062G10
10	0	T	P	P	T	P	P	T	P	P	P	9670A34G01	129A062G10
10	0	T	P	P	T	P	P	T	P	P	T	9670A97G01	129A062G10
10	0	T	P	T	P	P	P	P	P	P	P	1586C42G06	129A062G10
10	0	T	P	T	P	P	P	P	P	T	T	9682A79G01	129A062G10
10	0	T	P	T	P	P	P	P	T	P	T	1586C42G46	129A062G10
10	0	T	P	T	P	T	P	P	P	P	P	9676A87G01	129A062G10
10	0	T	P	T	P	T	P	T	P	P	P	9676A89G01	129A062G10
10	0	T	P	T	P	T	P	T	P	T	P	9668A54G01	129A062G10
10	0	T	P	T	T	T	P	T	P	T	P	9676A34G01	129A062G10

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
10	0	T	T	G	G	G	G	G	G	G	G	9689A49G01	129A062G10
10	0	T	T	G	G	G	G	T	T	T	T	9689A50G01	129A062G10
10	0	T	T	G	O	T	T	T	T	T	T	9682A41G01	129A062G10
10	0	T	T	G	T	T	T	T	T	T	T	9676A72G01	129A062G10
10	0	T	T	O	O	Y	Y	T	T	G	G	9688A10G01	129A062G10
10	0	T	T	P	P	P	P	P	P	P	P	1586C42G45	129A062G10
10	0	T	T	P	P	P	P	P	P	P	T	9667A78G01	129A062G10
10	0	T	T	P	P	P	P	P	P	P	W	991A814G01	129A062G10
10	0	T	T	P	P	P	P	P	P	T	P	9682A70G01	129A062G10
10	0	T	T	P	P	P	P	P	P	T	T	1586C42G41	129A062G10
10	0	T	T	P	P	P	P	T	T	P	P	9660A92G01	129A062G10
10	0	T	T	P	P	P	P	T	T	T	T	991A220G01	129A062G10
10	0	T	T	P	P	P	T	T	P	P	P	9671A68G01	129A062G10
10	0	T	T	P	P	T	P	P	P	P	P	9666A93G01	129A062G10
10	0	T	T	P	P	T	T	P	P	T	T	9667A86G01	129A062G10
10	0	T	T	P	P	T	T	P	T	T	P	991A221G01	129A062G10
10	0	T	T	T	G	G	T	P	P	Z	Z	9689A70G01	129A062G10
10	0	T	T	T	G	Y	Z	Y	O	O	Y	9666A52G01	129A062G10
10	0	T	T	T	O	O	O	O	O	O	O	9666A45G01	129A062G10
10	0	T	T	T	O	O	O	O	O	O	O	9682A35G01	129A062G10
10	0	T	T	T	P	P	P	P	P	P	P	9676A84G01	129A062G10
10	0	T	T	T	P	P	P	P	T	T	T	9663A25G01	129A062G10
10	0	T	T	T	P	P	P	T	T	P	P	991A222G01	129A062G10
10	0	T	T	T	P	P	P	W	P	P	T	991A929G01	129A062G10
10	0	T	T	T	P	T	T	P	T	T	P	991A230G01	129A062G10
10	0	T	T	T	P	Y	Y	Y	P	O	P	9682A38G01	129A062G10
10	0	T	T	T	T	O	O	O	O	O	O	9682A62G01	129A062G10
10	0	T	T	T	T	P	P	P	P	P	P	670B197G31	129A062G10
10	0	T	T	T	T	P	P	P	P	T	T	9682A60G01	129A062G10
10	0	T	T	T	T	P	P	T	T	T	T	9689A31G01	129A062G10
10	0	T	T	T	T	P	P	W	P	P	P	991A302G01	129A062G10
10	0	T	T	T	T	T	P	P	P	P	P	9671A13G01	129A062G10
10	0	T	T	T	T	T	T	G	G	O	O	9682A31G01	129A062G10
10	0	T	T	T	T	T	T	P	P	P	P	716B562G10	129A062G10
10	0	T	T	T	T	T	T	P	P	T	P	9666A65G01	129A062G10
10	0	T	T	T	T	T	T	P	P	Z	Z	9689A69G01	129A062G10
10	0	T	T	T	T	T	T	T	O	T	T	9689A60G01	129A062G10
10	0	T	T	T	T	T	T	T	P	P	P	9666A76G01	129A062G10
10	0	T	T	T	T	T	T	T	T	O	O	9682A66G01	129A062G10
10	0	T	T	T	T	T	T	T	T	P	P	1586C42G44	129A062G10
10	0	T	T	T	T	T	T	T	T	T	P	9666A43G01	129A062G10
10	0	T	T	T	T	T	T	T	T	T	T	129A539G01	129A062G10
10	0	T	T	T	T	T	T	T	T	T	W	9682A30G01	129A062G10
10	0	T	T	T	T	T	T	T	T	T	W	9682A67G01	129A062G10
10	0	T	T	T	T	T	T	T	T	W	W	9682A32G01	129A062G10
10	0	T	T	T	T	T	T	V	V	V	V	9682A90G01	129A062G10
10	0	T	T	T	T	T	T	Y	Y	Y	Y	9683A03G01	129A062G10
10	0	T	T	T	T	T	T	Z	Z	O	O	9682A96G01	129A062G10
10	0	T	T	T	T	T	T	Z	Z	Z	Z	9672A02G01	129A062G10
10	0	T	T	T	T	T	Z	Z	Z	Z	Z	9683A06G01	129A062G10
10	0	T	T	T	T	W	W	W	W	W	W	9682A99G01	129A062G10
10	0	T	T	T	T	Z	T	T	T	T	T	9664A79G01	129A062G10
10	0	T	T	T	T	Z	Z	Z	G	G	G	9689A61G01	129A062G10
10	0	T	T	T	T	Z	Z	Z	Z	Z	Z	9688A93G01	129A062G10

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
		A	B	C	D	E	F	G	H	I	J		
10	0	T	T	T	Y	Y	P	P	P	P	P	9676A74G01	129A062G10
10	0	T	T	T	Z	Z	T	T	T	T	T	9664A78G01	129A062G10
10	0	T	T	Y	Y	P	P	P	P	P	P	9676A73G01	129A062G10
10	0	T	T	Y	Y	Z	Z	Z	Z	T	P	9689A08G01	129A062G10
10	0	T	T	Z	Z	P	P	T	G	O	G	9664A88G01	129A062G10
10	0	T	T	Z	Z	T	T	T	T	T	T	9682A29G01	129A062G10
10	0	T	T	Z	Z	T	T	T	T	T	T	9682A37G01	129A062G10
10	0	T	T	Z	Z	Z	Z	Z	Z	Z	Z	9652A26G01	129A062G10
10	0	T	W	P	P	P	P	P	P	P	P	9666A47G01	129A062G10
10	0	T	W	P	W	T	T	W	P	W	T	991A303G01	129A062G10
10	0	T	W	W	W	W	P	P	P	P	P	9682A52G01	129A062G10
10	0	T	Y	Z	P	P	P	P	P	O	O	9666A36G01	129A062G10
10	0	T	Y	Z	T	Y	Z	T	Y	Z	P	9689A40G01	129A062G10
10	0	T	Y	Z	W	G	G	G	G	G	G	9689A36G01	129A062G10
10	0	T	Y	Z	W	G	G	G	G	G	P	9688A54G01	129A062G10
10	0	T	Y	Z	W	P	P	P	G	G	G	9688A52G01	129A062G10
10	0	T	Y	Z	W	P	P	P	P	P	P	9688A53G01	129A062G10
10	0	T	Y	Z	W	T	Y	Z	W	P	P	9666A13G01	<1>
10	0	T	Z	P	O	T	G	W	P	O	G	9664A84G01	129A062G10
10	0	W	W	O	O	Y	Y	Z	Z	Y	W	9647A22G01	129A062G10
10	0	W	W	P	P	G	G	P	P	P	P	9669A33G01	129A062G10
10	0	W	W	P	P	P	P	P	P	P	P	991A232G01	129A062G10
10	0	W	W	T	T	T	G	P	P	P	P	9647A21G01	129A062G10
10	0	W	W	T	T	Y	Z	Y	O	O	P	9666A53G01	129A062G10
10	0	W	W	T	T	Y	Z	Y	O	O	Y	9649A37G01	129A062G10
10	0	W	W	W	T	T	T	T	T	T	T	9641A64G01	129A062G10
10	0	W	W	W	W	W	W	W	W	W	T	9646A77G01	129A062G10
10	0	W	W	W	W	W	W	W	W	W	W	9676A93G01	129A062G10
10	0	W	W	W	W	W	Y	Y	Y	Y	Y	9689A63G01	129A062G10
10	0	W	W	W	W	Y	Y	Y	Y	G	G	9688A66G01	129A062G10
10	0	W	Y	Z	Z	Y	Y	G	T	T	T	9683A17G01	129A062G10
10	0	W	Y	Z	Z	Y	Y	O	W	W	W	9683A19G01	129A062G10
10	0	Y	G	Y	G	Y	Y	Y	W	W	W	9688A14G01	129A062G10
10	0	Y	T	G	W	Z	W	T	T	T	P	9666A79G01	129A062G10
10	0	Y	Y	T	T	T	T	T	T	T	T	9666A87G01	129A062G10
10	0	Y	Y	W	W	W	W	W	W	W	W	9688A82G01	129A062G10
10	0	Y	Y	W	W	W	W	Y	Y	Y	Y	9688A73G01	129A062G10
10	0	Y	Y	W	W	Y	Y	W	Y	Y	Y	9688A72G01	129A062G10
10	0	Y	Y	Y	Y	T	T	T	T	T	T	9666A86G01	129A062G10
10	0	Y	Y	Y	Y	W	W	W	W	T	T	9669A41G01	129A062G10
10	0	Y	Y	Y	Y	W	W	W	W	W	W	9688A71G01	129A062G10
10	0	Y	Y	Y	Y	W	W	Y	Y	Y	Y	9689A47G01	129A062G10
10	0	Y	Y	Y	Y	Y	T	T	T	T	T	9688A09G01	129A062G10
10	0	Y	Y	Y	Y	Y	W	W	W	W	W	9688A81G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	P	P	P	P	9669A38G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	T	T	P	P	9682A46G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	W	W	W	W	9688A78G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	W	W	Y	Y	9688A80G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	Y	T	T	T	9689A13G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	Y	G	G	G	9688A24G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	Y	T	T	T	9666A90G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	Y	W	W	W	9688A77G01	129A062G10
10	0	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	9683A01G01	129A062G10
10	0	Y	Y	Z	Z	Z	Z	Z	Z	T	P	9689A09G01	129A062G10

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug	
A	B	C	D	E	F	G	H	I	J					
10	0	Z	Z	G	G	G	G	G	G	G	G	9666A77G01	129A062G10	
10	0	Z	Z	G	G	G	G	G	W	W	W	9683A75G01	129A062G10	
10	0	Z	Z	G	G	G	G	W	W	W	Y	9683A70G01	129A062G10	
10	0	Z	Z	G	G	W	W	W	W	W	W	9688A23G01	129A062G10	
10	0	Z	Z	G	G	W	W	Y	Y	Y	Y	9652A27G01	129A062G10	
10	0	Z	Z	G	G	W	Y	Y	Y	W	W	9688A74G01	129A062G10	
10	0	Z	Z	P	P	P	P	P	P	P	P	9682A65G01	129A062G10	
10	0	Z	Z	P	P	W	W	P	P	P	P	991A943G01	129A062G10	
10	0	Z	Z	W	W	W	W	W	W	W	W	9688A76G01	129A062G10	
10	0	Z	Z	W	W	W	W	W	Y	Y	Y	9683A02G01	129A062G10	
10	0	Z	Z	Y	Y	Y	Y	W	W	W	W	9666A92G01	129A062G10	
10	0	Z	Z	Y	Y	Y	Y	Y	Y	G	W	9663A41G01	129A062G10	
10	0	Z	Z	Y	Y	Y	Y	Y	Y	W	W	9682A78G01	129A062G10	
10	0	Z	Z	Z	O	O	O	O	O	O	O	9688A89G01	129A062G10	
10	0	Z	Z	Z	P	P	P	P	P	P	P	9682A89G01	129A062G10	
10	0	Z	Z	Z	T	T	T	T	T	T	Z	991A227G01	129A062G10	
10	0	Z	Z	Z	Z	O	O	O	O	O	O	9688A88G01	129A062G10	
10	0	Z	Z	Z	Z	P	P	P	P	P	P	9682A64G01	129A062G10	
10	0	Z	Z	Z	Z	T	T	T	T	T	T	9669A39G01	129A062G10	
10	0	Z	Z	Z	Z	Z	O	O	O	O	O	9689A15G01	129A062G10	
10	0	Z	Z	Z	Z	Z	Z	O	O	O	O	9688A92G01	129A062G10	
10	0	Z	Z	Z	Z	Z	Z	T	T	T	T	9682A19G01	129A062G10	
10	0	Z	Z	Z	Z	Z	Z	Z	Z	O	O	9689A91G01	129A062G10	
10	0	Z	Z	Z	Z	Z	Z	Z	Z	P	P	9676A81G01	129A062G10	
10	0	Z	Z	Z	Z	Z	Z	Z	Z	W	W	9676A91G01	129A062G10	
10	0	Z	Z	Z	Z	Z	Z	Z	Z	Z	Z	9676A94G01	129A062G10	
9	1	C	P	P	P	P	P	P	P	P	P	498A011G01	<1>	
9	1	C	T	T	T	T	T	T	T	T	T	1586C42G39	<1>	
9	1	O	Y	C	W	G	P	P	T	T	T	9647A19G01	129A062G10	
8	2	C	-	A	P	P	P	P	P	P	P	714B325G31	<1>	
8	2	C	-	A	T	T	T	T	T	T	T	9682A80G01	<1>	
8	2	C	-	C	P	P	P	P	P	P	P	837A665G01	<1>	
8	2	C	-	C	P	P	P	P	T	T	T	9647A12G01	<1>	
8	2	C	-	C	P	P	T	T	T	T	T	9647A11G01	<1>	
8	2	C	-	C	T	T	P	P	P	P	P	9676A86G01	<1>	
8	2	C	-	C	T	T	P	P	T	T	P	9688A07G01	<1>	
8	2	C	-	C	T	T	T	T	P	P	P	9647A98G01	<1>	
8	2	C	-	C	T	T	T	T	T	T	P	9683A72G01	<1>	
8	2	C	-	C	T	T	T	T	T	T	T	1586C42G20	<1>	
8	2	C	-	C	Z	Z	Z	Z	Z	Z	Z	991A944G01	<1>	
8	2	O	Y	Z	W	G	C	-	C	T	V	H	991A934G01	<1>
8	2	P	C	C	P	P	P	T	P	P	P	1586C42G32	<1>	
8	2	P	P	C	-	C	P	P	P	P	P	670B197G33	<1>	
8	2	P	P	P	C	-	C	P	P	P	P	716B562G21	<1>	
8	2	P	P	P	P	P	C	-	C	P	P	9689A72G01	<1>	
8	2	P	P	P	P	P	P	8	-	8	Z	Z	9666A28G01	<1>
8	2	P	P	P	P	P	P	C	-	C	P	P	9663A60G01	<1>
8	2	P	P	P	P	P	P	P	C	-	B	P	9666A82G01	<1>
8	2	P	P	P	P	P	P	P	C	-	C	P	129A542G01	129A062G01
8	2	P	P	P	P	P	P	P	C	-	C	T	1586C42G38	129A062G01
8	2	P	P	P	P	P	P	P	P	C	-	A	714B325G30	<1>
8	2	P	P	P	P	P	P	P	P	C	-	C	716B562G26	<1>
8	2	P	P	P	P	P	P	P	P	C	-	E	9682A25G01	&

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug			
		A	B	C	D	E	F	G	H	I	J					
8	2	P	P	P	P	P	T	T	T	C	-	C	991A241G01	<1>		
8	2	P	P	P	P	T	T	P	C	-	C	P	716B562G35	129A062G01		
8	2	P	P	P	R	-	R	P	P	P	P	P	9682A74G01	<1>		
8	2	P	P	P	T	T	T	T	C	-	C	P	9666A42G01	129A062G01		
8	2	P	P	P	T	T	T	T	T	C	-	C	991A226G01	<1>		
8	2	P	P	R	-	R	T	P	P	P	P	P	9689A25G01	<1>		
8	2	P	P	T	T	T	T	T	T	C	-	C	9688A98G01	<1>		
8	2	T	P	P	P	P	P	P	C	-	C	P	9672A83G01	129A062G01		
8	2	T	P	P	P	P	P	P	C	-	C	T	1586C42G26	129A062G01		
8	2	T	T	C	-	C	P	G	Y	W	Z	O	9676A04G01	<1>		
8	2	T	T	R	-	A	T	T	T	T	T	T	9689A87G01	<1>		
8	2	T	T	R	-	R	T	T	T	T	T	T	991A933G01	<1>		
8	2	T	T	T	C	-	C	P	P	P	P	P	9666A69G01	<1>		
8	2	T	T	T	S	T	S	O	O	G	G	G	9689A88G01	<1>		
8	2	T	T	T	T	C	-	C	T	T	T	T	1586C42G33	<1>		
8	2	T	T	T	T	T	T	5	-	5	P	P	9682A85G01	<1>		
8	2	T	T	T	T	T	T	C	-	A	T	T	9688A62G01	<1>		
8	2	T	T	T	T	T	T	R	-	R	T	T	9666A34G01	<1>		
8	2	T	T	T	T	T	T	T	C	-	C	T	1586C42G47	129A062G01		
8	2	T	T	T	T	T	T	T	R	-	A	T	9666A96G01	129A062G01		
8	2	T	T	T	T	T	T	T	R	-	R	T	670B197G17	129A062G01		
8	2	T	T	T	T	T	T	T	T	C	-	C	9672A89G01	<1>		
7	3	P	P	P	P	P	P	C	C	-	C	P	129A553G01	<1>		
6	4	6	-	6	7	-	7	G	Y	Z	W	O	W	9666A27G01	<1>	
6	4	C	C	P	P	P	P	P	P	C	C	C	716B562G20	<1>		
6	4	C	-	A	C	-	A	P	P	P	P	P	P	714B325G27	<1>	
6	4	C	-	C	C	-	C	P	P	P	P	P	O	991A622G01	<1>	
6	4	C	-	C	C	-	C	P	P	P	P	P	P	498A015G01	<1>	
6	4	C	-	C	C	-	C	P	P	P	P	P	T	1586C42G13	<1>	
6	4	C	-	C	C	-	C	P	P	P	P	T	T	9672A80G01	<1>	
6	4	C	-	C	C	-	C	P	P	P	T	T	T	991A218G01	<1>	
6	4	C	-	C	C	-	C	P	P	T	T	T	T	9676A06G01	<1>	
6	4	C	-	C	C	-	C	T	T	P	P	P	P	991A334G01	<1>	
6	4	C	-	C	C	-	C	T	T	T	T	T	T	9663A31G01	<1>	
6	4	C	-	C	P	P	C	-	C	P	P	P	P	716B562G17	<1>	
6	4	C	-	C	P	P	P	P	C	-	C	P	P	716B562G19	<1>	
6	4	C	-	C	P	P	P	P	P	P	C	-	C	877A077G01	<1>	
6	4	C	-	C	T	T	T	C	-	C	T	T	T	9666A97G01	<1>	
6	4	C	-	C	-	C	-	A	T	T	T	T	T	9683A94G01	<1>	
6	4	C	-	C	-	C	-	C	P	P	P	P	P	1586C42G11	<1>	
6	4	C	-	C	-	C	-	C	P	P	P	P	T	1586C42G12	<1>	
6	4	C	-	C	-	C	-	C	T	T	T	T	T	9672A99G01	<1>	
6	4	C	-	C	-	C	-	C	W	W	W	T	T	9689A38G01	<1>	
6	4	C	-	C	-	C	-	E	T	T	T	T	T	9672A87G01	<1>	
6	4	O	O	P	P	P	P	R	-	6	-	7	-	C	9666A37G01	<1>
6	4	P	C	-	C	C	-	C	P	P	P	P	P	716B562G36	<1>	
6	4	P	C	-	C	C	-	C	T	T	T	T	T	9682A36G01	<1>	
6	4	P	C	-	C	P	P	P	P	C	-	C	P	129A513G01	129A062G06	
6	4	P	C	-	C	P	P	P	P	C	-	C	T	629A735G01	129A062G06	
6	4	P	C	-	C	P	P	P	T	C	-	C	P	1586C42G22	129A062G06	
6	4	P	C	-	C	P	P	T	T	C	-	C	T	1586C42G27	129A062G06	
6	4	P	C	-	C	-	C	-	C	P	P	P	P	836A867G01	<1>	
6	4	P	P	C	P	C	P	C	P	C	P	C	P	991A506G01	292B319G22	
6	4	P	P	C	-	A	C	-	A	P	P	P	P	714B325G28	<1>	

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug			
		A	B	C	D	E	F	G	H	I	J					
6	4	P	P	C	-	C	P	P	C	-	C	P	P	716B562G15	<1>	
6	4	P	P	P	C	-	C	C	-	C	P	P	P	9689A81G01	129A062G12	
6	4	P	P	P	C	-	C	C	-	T	T	T		9652A30G01	129A062G12	
6	4	P	P	P	C	-	C	P	P	C	-	C	P	129A520G01	129A062G05	
6	4	P	P	P	C	-	C	-	C	C	P	P	P	991A335G01	<1>	
6	4	P	P	P	P	C	C	C	C	C	P	P	P	9689A01G01	<1>	
6	4	P	P	P	P	C	-	A	C	-	A	P	P	714B325G29	<1>	
6	4	P	P	P	P	C	-	C	C	-	C	P	P	670B197G19	<1>	
6	4	P	P	P	P	C	-	C	P	P	C	-	C	670B197G34	<1>	
6	4	P	P	P	P	P	C	-	C	C	-	C	P	129A532G01	129A062G02	
6	4	P	P	P	P	P	P	C	-	A	C	-	A	714B325G16	<1>	
6	4	P	P	P	P	P	P	C	-	C	-	C	-	714B325G18	<1>	
6	4	P	P	P	P	P	P	C	-	C	-	C	-	670B197G28	<1>	
6	4	P	P	T	P	P	C	-	C	C	-	C	P	9676A09G01	129A062G02	
6	4	P	P	T	P	T	P	C	-	C	-	C	-	1586C42G14	<1>	
6	4	P	T	P	R	-	C	P	P	R	-	C	P	9676A71G01	129A062G05	
6	4	R	-	A	R	-	A	T	T	T	T	T	T	9689A73G01	<1>	
6	4	R	-	R	R	-	R	O	O	O	O	O	O	9682A98G01	<1>	
6	4	R	-	R	R	-	R	T	T	T	T	T	T	670B197G25	<1>	
6	4	T	P	C	P	C	P	C	P	C	P	C	P	670B197G37	292B319G22	
6	4	T	P	P	C	-	C	P	P	C	-	C	P	9660A91G01	129A062G05	
6	4	T	P	P	C	-	C	T	P	P	C	-	C	9676A05G01	<1>	
6	4	T	P	P	P	P	C	-	C	C	-	C	T	849A307G01	<1>	
6	4	T	R	-	E	T	R	-	E	T	T	T	T	991A231G01	<1>	
6	4	T	T	T	R	-	R	T	T	R	-	R	T	861A670G01	129A062G05	
6	4	T	T	T	T	T	T	C	-	C	C	-	C	991A235G01	<1>	
6	4	T	Y	Z	T	Y	Z	R	-	6	-	7	-	C	9689A42G01	<1>
6	4	Z	Z	O	O	O	O	C	-	C	C	-	C	9689A18G01	<1>	
5	5	P	P	C	C	-	C	P	C	-	C	P	P	670B197G20	<1>	
4	6	7	-	7	7	-	7	7	-	7	P	P	O	O	9682A48G01	<1>
4	6	7	-	7	7	-	7	7	-	7	T	T	T	T	9682A49G01	<1>
4	6	7	-	7	7	-	7	7	-	7	Y	Y	Y	Y	9682A50G01	<1>
4	6	8	-	8	8	-	8	8	-	8	W	W	W	W	9682A51G01	<1>
4	6	9	-	9	9	-	9	9	-	9	P	P	P	P	9669A43G01	<1>
4	6	9	-	9	9	-	9	9	-	9	W	W	W	W	9669A36G01	<1>
4	6	C	C	C	C	C	C	C	P	P	P	P	P	774B430G18	<1>	
4	6	C	C	-	C	-	C	C	T	T	T	T	T	1586C42G21	<1>	
4	6	C	-	C	5	-	5	R	-	R	P	P	P	P	9666A91G01	<1>
4	6	C	-	C	C	-	C	C	-	C	G	T	T	T	9683A15G01	<1>
4	6	C	-	C	C	-	C	C	-	C	O	O	W	W	9683A21G01	<1>
4	6	C	-	C	C	-	C	C	-	C	O	Y	W	W	9683A20G01	<1>
4	6	C	-	C	C	-	C	C	-	C	P	P	P	P	774B430G20	<1>
4	6	C	-	C	C	-	C	C	-	C	P	P	P	T	1586C42G36	<1>
4	6	C	-	C	C	-	C	C	-	C	P	P	T	T	9671A70G01	<1>
4	6	C	-	C	C	-	C	C	-	C	T	T	P	P	9683A73G01	<1>
4	6	C	-	C	C	-	C	C	-	C	T	T	T	T	774B430G24	<1>
4	6	C	-	C	C	-	C	C	-	C	T	T	W	W	991A238G01	<1>
4	6	C	-	C	C	-	C	C	-	C	Y	Y	Z	Z	991A239G01	<1>
4	6	C	-	C	C	-	C	C	-	C	Z	Z	Y	Y	9666A60G01	<1>
4	6	C	-	C	P	P	C	-	C	P	P	C	-	C	716B562G16	<1>
4	6	C	-	C	T	P	C	-	C	-	C	C	P	T	1586C42G10	<1>
4	6	C	-	C	-	C	-	C	C	-	C	P	P	P	774B430G09	<1>
4	6	C	-	C	-	C	-	C	C	-	C	P	T	P	9676A98G01	<1>
4	6	C	-	C	-	C	-	D	P	L	C	-	C	T	9683A98G01	<1>

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
4	6	G	G	9	9	9	9	9	9	P	P	9669A42G01	<1>
4	6	L	L	L	L	C	E	C	E	C	E	9660A96G01	<1>
4	6	O	G	T	W	C	C	C	C	C	C	9676A99G01	<1>
4	6	O	O	O	O	C	C	C	C	C	C	9689A14G01	<1>
4	6	O	Y	Y	O	C	C	C	C	C	C	9666A20G01	<1>
4	6	O	Y	Z	8	9	8	6	8	7	P	9683A05G01	292B319G23
4	6	P	C	A	P	C	A	P	C	A	P	9689A04G01	<1>
4	6	P	C	C	C	C	C	P	P	P	P	716B562G37	129A062G09
4	6	P	C	C	C	C	C	P	P	P	P	774B430G10	129A062G09
4	6	P	C	C	P	C	C	P	C	C	P	129A528G01	<1>
4	6	P	G	T	C	C	5	5	R	R	W	9676A58G01	292B319G23
4	6	P	P	C	C	C	C	C	C	P	P	774B430G21	<1>
4	6	P	P	C	C	C	C	C	P	P	P	714B325G19	<1>
4	6	P	P	C	C	P	P	C	C	C	C	716B562G18	<1>
4	6	P	P	P	6	6	6	6	6	6	P	9664A93G01	292B319G23
4	6	P	P	P	C	C	C	C	C	C	P	9670A05G01	<1>
4	6	P	P	P	C	A	C	A	C	A	P	9688A22G01	292B319G23
4	6	P	P	P	C	A	P	C	C	C	A	714B325G17	<1>
4	6	P	P	P	C	C	C	C	C	C	P	129A514G01	292B319G23
4	6	P	P	P	C	C	C	C	C	C	T	670B197G32	292B319G23
4	6	P	P	P	C	C	C	C	C	C	Z	9671A93G01	292B319G23
4	6	P	P	P	C	C	C	R	C	R	T	1586C42G34	292B319G23
4	6	P	P	P	C	C	P	C	C	C	C	670B197G27	<1>
4	6	P	P	P	G	R	R	R	R	R	R	9688A01G01	<1>
4	6	P	P	P	P	C	A	C	A	C	A	714B325G24	<1>
4	6	P	P	P	P	C	B	C	B	C	B	9666A46G01	<1>
4	6	P	P	P	P	C	C	C	C	C	C	1586C42G05	<1>
4	6	P	P	P	P	C	C	C	C	C	C	670B197G18	<1>
4	6	P	P	P	P	C	C	C	C	C	C	1586C42G37	<1>
4	6	P	P	P	P	P	P	C	C	C	C	670B197G23	<1>
4	6	P	P	P	P	R	R	R	R	R	R	9660A85G01	<1>
4	6	P	P	P	R	R	R	R	R	R	P	1586C42G03	292B319G23
4	6	P	P	P	R	R	R	R	R	R	W	9688A38G01	292B319G23
4	6	P	P	T	C	C	C	C	C	C	T	1586C42G48	292B319G23
4	6	P	R	R	P	R	R	P	R	R	P	9676A17G01	<1>
4	6	P	T	Z	C	7	8	7	7	C	P	9676A55G01	292B319G23
4	6	P	T	Z	C	8	R	8	7	8	W	9676A68G01	292B319G23
4	6	P	T	Z	W	6	5	8	5	9	5	9689A53G01	<1>
4	6	P	Y	Y	P	C	C	C	C	C	C	9666A55G01	<1>
4	6	P	Y	Z	R	R	6	6	7	6	P	9666A63G01	292B319G23
4	6	P	Y	Z	R	R	6	6	7	7	P	9666A67G01	292B319G23
4	6	R	B	R	B	R	B	T	T	T	T	714B325G20	<1>
4	6	R	R	7	7	C	C	G	Y	T	P	9664A89G01	<1>
4	6	R	R	7	7	C	C	G	Y	W	O	9664A81G01	<1>
4	6	R	R	7	7	C	C	T	G	O	G	9664A87G01	<1>
4	6	R	R	7	7	C	C	T	T	T	P	991A941G01	<1>
4	6	R	R	7	7	C	C	T	Z	P	O	9664A86G01	<1>
4	6	R	R	7	7	C	C	W	P	O	G	9666A88G01	<1>
4	6	R	R	7	7	C	C	W	P	T	G	9664A85G01	<1>
4	6	R	R	7	7	C	C	Y	W	T	G	9666A84G01	<1>
4	6	R	R	R	R	R	R	P	P	P	P	9689A33G01	<1>
4	6	R	R	R	R	R	R	T	T	T	T	9688A11G01	<1>
4	6	T	5	A	T	5	A	T	5	A	T	9689A28G01	<1>
4	6	T	C	C	C	C	C	P	P	P	P	9676A60G01	129A062G09
Poten- tials	Cur- rents	A	B	C	D	E	F	G	H	I	J	Style No.	In-Service Test Plug
4	6	T	C	C	T	C	C	T	C	C	T	188A523G01	<1>
4	6	T	C	C	T	C	C	T	C	C	Y	9689A84G01	<1>
4	6	T	O	G	W	R	R	9	9	5	5	9666A72G01	<1>
4	6	T	P	C	C	C	C	C	C	P	P	1586C42G18	<1>
4	6	T	P	P	C	C	C	C	C	C	P	9682A53G01	292B319G23
4	6	T	P	P	P	C	C	C	C	C	C	9664A80G01	<1>
4	6	T	P	P	P	C	C	C	R	C	C	9689A89G01	<1>
4	6	T	P	T	P	C	C	C	C	C	C	9666A94G01	<1>
4	6	T	P	Z	W	R	R	C	C	7	7	9688A87G01	<1>
4	6	T	T	C	C	C	C	C	C	T	T	9667A22G01	<1>
4	6	T	T	P	C	C	C	C	C	C	P	9689A07G01	292B319G23
4	6	T	T	P	C	C	C	C	C	C	T	9667A80G01	292B319G23
4	6	T	T	P	P	C	C	C	C	C	C	9672A90G01	<1>
4	6	T	T	T	5	5	5	5	5	5	T	9682A84G01	292B319G23
4	6	T	T	T	5	A	5	A	5	A	T	9689A29G01	292B319G23
4	6	T	T	T	C	C	C	C	C	C	G	9666A59G01	292B319G23
4	6	T	T	T	C	C	C	C	C	C	P	9667A69G01	292B319G23
4	6	T	T	T	C	C	C	C	C	C	T	714B325G32	292B319G23
4	6	T	T	T	C	C	C	C	C	C	W	9676A35G01	292B319G23
4	6	T	T	T	G	C	C	C	C	C	C	9647A23G01	<1>
4	6	T	T	T	P	C	C	C	C	C	C	9676A80G01	<1>
4	6	T	T	T	R	R	R	R	R	R	T	774B430G13	292B319G23
4	6	T	T	T	T	C	C	C	C	C	C	498A010G01	<1>
4	6	T	T	T	T	C	C	C	C	C	C	9676A10G01	<1>
4	6	T	T	T	T	R	R	8	8	7	7	9682A69G01	<1>
4	6	T	T	T	T	R	R	R	R	R	R	9682A39G01	<1>
4	6	T	W	Z	G	R	R	7	7	8	8	9688A41G01	<1>
4	6	T	W	Z	G	R	R	8	8	7	7	9683A07G01	<1>
4	6	T	W	Z	P	R	R	8	8	7	7	991A234G01	<1>
4	6	T	W	Z	R	R	8	8	7	7	P	9683A04G01	292B319G23
4	6	T	Y	P	G	R	R	6	6	C	C	9682A86G01	<1>
4	6	T	Y	Z	8	C	P	R	6	7	C	9689A41G01	<1>
4	6	T	Y	Z	R	R	6	6	7	7	P	9666A44G01	292B319G23
4	6	T	Y	Z	W	C	C	C	C	C	C	9689A06G01	<1>
4	6	W	W	O	O	C	C	C	C	C	C	9666A54G01	<1>
4	6	W	W	O	Y	C	C	C	C	C	C	9666A21G01	<1>
4	6	W	W	W	9	C	9	C	9	C	W	9652A25G01	292B319G23
4	6	W	W	W	W	8	8	8	8	8	8	9682A93G01	<1>
4	6	W	W	W	W	9	9	9	9	9	9	991A624G01	<1>
4	6	W	W	W	W	C	C	C	C	C	C	9688A02G01	<1>
4	6	W	W	Y	O	C	C	C	C	C	C	9647A20G01	<1>
4	6	W	Y	Y	O	C	C	C	C	C	C	9652A28G01	<1>
4	6	Y	T	G	6	6	R	R	5	5	W	9666A66G01	292B319G23
4	6	Y	Y	Y	C	C	C	C	C	C	Y	991A236G01	292B319G23
4	6	Y	Y	Y	R	R	R	R	R	R	Y	9669A30G01	292B319G23
4	6	Z	R	R	Z	R	R	Z	R	R	P	9666A38G01	<1>
4	6	Z	Z	O	O	C	C	C	C	C	C	9689A19G01	<1>
4	6	Z	Z	Z	C	C	C	C	C	C	Z	9672A01G01	292B319G23
4	6	Z	Z	Z	R	R	R	R	R	R	G	9682A82G01	292B319G23
4	6	Z	Z	Z	R	R	R	R	R	R	Z	991A240G01	292B319G23
4	6	Z	Z	Z	W	R	R	6	6	5	5	9689A85G01	<1>
4	6	Z	Z	Z	Z	C	C	C	C	C	C	9676A95G01	<1>
3	7	9	C	6	C	7	C	8	P	G	P	9683A96G01	<1>
3	7	C	Y	Y	Y	C	C	C	C	C	C	9682A97G01	<1>

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug
3	7	C	C	C	C	C	C	P	P	P	P	1586C42G43	<1>
3	7	C	C	P	C	C	P	C	C	P	C	714B325G22	<1>
3	7	L	L	L	U	C	E	C	E	C	E	1485B70G10	<1>
3	7	P	G	T	C	C	5	5	R	R	8	9676A76G01	<1>
3	7	P	P	C	C	C	C	C	C	C	P	716B562G12	<1>
3	7	P	P	C	C	C	C	C	C	C	P	129A535G01	292B319G22
3	7	P	P	C	C	C	C	C	C	T		9672A86G01	292B319G22
3	7	P	P	P	C	C	C	C	C	C	C	1586C42G17	<1>
3	7	P	P	P	C	C	C	C	C	C	C	9671A26G01	<1>
3	7	P	P	P	C	B	C	B	C	B	S	716B562G30	<1>
3	7	P	P	P	C	C	C	C	C	C	C	1586C42G19	<1>
3	7	P	P	P	C	C	C	C	C	C	C	714B325G11	<1>
3	7	P	P	P	C	C	C	C	C	C	C	714B325G25	<1>
3	7	P	P	P	S	C	C	C	C	C	C	774B430G16	<1>
3	7	P	P	P	U	C	U	C	U	C	U	1485B70G09	<1>
3	7	P	T	C	C	C	C	C	C	T		670B197G22	292B319G22
3	7	R	R	7	7	C	C	C	Y	W	O	9666A89G01	<1>
3	7	T	O	Y	S	C	8	7	8	5	8	9666A56G01	<1>
3	7	T	T	C	C	C	C	C	C	T		670B197G35	292B319G22
3	7	T	T	C	C	C	C	C	C	T		9688A86G01	<1>
3	7	T	T	T	C	C	5	5	R	R	8	9689A45G01	<1>
3	7	T	T	T	C	C	C	C	C	C	C	9663A59G01	<1>
3	7	T	T	T	C	C	C	C	C	N		291B961G25	<1>
3	7	T	T	T	C	C	C	C	C	U		1485B70G11	<1>
3	7	T	T	T	R	R	R	R	R	R	R	9688A50G01	<1>
2	8	5	5	5	5	5	5	5	5	G	G	9683A87G01	<1>
2	8	6	6	R	R	5	5	8	8	Z	W	9666A64G01	<1>
2	8	7	7	7	7	7	7	7	7	W	W	9682A47G01	<1>
2	8	7	7	7	7	7	7	7	7	Z	Z	9683A89G01	<1>
2	8	8	C	8	C	8	C	8	C	P	P	991A237G01	<1>
2	8	8	C	R	C	5	C	9	C	T	T	9688A85G01	<1>
2	8	9	9	9	9	9	9	9	9	G	G	9669A35G01	<1>
2	8	9	C	6	C	7	C	C	C	T	T	9647A18G01	<1>
2	8	C	C	C	C	C	C	C	C	P	P	9689A02G01	<1>
2	8	C	A	P	P	C	C	C	C	C	C	714B325G21	<1>
2	8	C	B	C	B	C	B	C	B	P	P	991A942G01	<1>
2	8	C	C	C	C	C	C	C	C	P	P	837A407G01	<1>
2	8	C	C	C	C	C	C	C	C	P	T	9672A95G01	<1>
2	8	C	C	C	C	C	C	C	C	T	P	9676A11G01	<1>
2	8	C	C	C	C	C	C	C	C	T	T	774B430G22	<1>
2	8	C	C	C	C	C	C	C	C	W	W	9683A16G01	<1>
2	8	C	C	C	C	P	C	C	C	C	P	837A664G01	<1>
2	8	C	C	P	P	C	C	C	C	C	C	716B562G24	<1>
2	8	C	C	T	C	C	C	C	C	C	P	9688A94G01	<1>
2	8	C	C	T	C	C	C	C	C	C	T	9667A68G01	<1>
2	8	C	C	C	B	C	C	C	B	P	P	498A031G01	<1>
2	8	C	C	C	C	C	C	C	C	P	P	716B562G38	<1>
2	8	C	C	C	C	C	C	C	C	P	P	714B325G15	<1>
2	8	C	C	C	C	C	C	C	B	P	P	837A101G01	<1>
2	8	C	C	C	C	C	C	C	B	T	T	1586C42G42	<1>
2	8	C	C	C	C	C	C	C	C	P	P	774B430G11	<1>
2	8	C	C	C	C	C	C	C	C	P	T	1586C42G09	<1>
2	8	C	C	C	C	C	C	C	C	T	P	9671A22G01	<1>
2	8	C	C	C	C	C	C	C	C	T	T	9642A36G01	<1>

Poten- tials	Cur- rents	Arrangement										Style No.	In-Service Test Plug	
		A	B	C	D	E	F	G	H	I	J			
2	8	C	C	C	C	C	P	C	C	C	C	P	9672A94G01	<1>
2	8	C	C	C	C	T	C	C	C	C	T		9676A01G01	<1>
2	8	C	C	C	D	C	C	C	B	P	P		498A032G01	<1>
2	8	C	C	C	D	C	C	C	D	P	P		714B325G13	<1>
2	8	C	C	C	D	C	C	C	D	P	P		774B430G12	<1>
2	8	C	C	C	E	C	C	C	E	T	T		9672A23G01	<1>
2	8	C	C	C	E	T	C	C	C	E	T		9672A88G01	<1>
2	8	C	C	E	C	C	C	C	C	P	P		716B562G39	<1>
2	8	L	C	E	C	E	C	E	C	E	L		9666A23G01	<1>
2	8	O	O	C	C	C	C	C	C	C	C		9682A61G01	<1>
2	8	P	8	8	8	8	8	8	8	8	P		9682A24G01	292B319G22
2	8	P	C	C	C	C	C	C	C	C	P		129A519G01	<1>
2	8	P	C	C	C	C	P	C	C	C	C		716B562G27	<1>
2	8	P	C	C	C	C	C	C	C	C	P		129A518G01	292B319G22
2	8	P	C	C	C	C	C	C	C	C	T		1586C42G08	292B319G22
2	8	P	C	C	C	C	C	C	C	C	T		837A616G01	292B319G22
2	8	P	P	5	5	R	R	6	6	C	C		9682A87G01	<1>
2	8	P	P	9	9	9	9	9	9	9	9		991A625G01	<1>
2	8	P	P	C	C	C	C	C	C	C	C		716B562G25	<1>
2	8	P	P	C	C	C	C	C	C	C	C		9676A96G01	<1>
2	8	P	R	R	8	8	7	7	C	C	P		991A233G01	292B319G22
2	8	P	R	R	R	R	R	R	R	R	P		9683A99G01	292B319G22
2	8	P	S	P	R	R	R	R	R	R	C		9676A83G01	<1>
2	8	R	6	7	C	R	6	7	C	O	O		9666A35G01	<1>
2	8	R	B	R	B	R	B	R	B	T	T		714B325G12	<1>
2	8	R	C	R	C	R	C	R	C	T	T		716B562G11	<1>
2	8	R	R	7	7	C	C	9	9	T	G		9664A83G01	<1>
2	8	R	R	7	7	C	C	9	9	T	P		9664A82G01	<1>
2	8	R	R	R	R	R	R	R	R	P	P		9688A91G01	<1>
2	8	R	R	R	R	R	R	R	R	T	T		9666A48G01	<1>
2	8	T	5	5	6	6	7	7	5	5	T		9666A26G01	292B319G22
2	8	T	C	C	C	C	C	C	C	C	P		9671A04G01	<1>
2	8	T	C	C	C	C	C	C	C	C	T		9671A12G01	<1>
2	8	T	C	C	C	C	C	C	C	T			876A157G01	<1>
2	8	T	C	C	C	C	C	C	C	C	P		670B197G38	292B319G22
2	8	T	C	C	C	C	C	C	C	C	T		849A513G01	292B319G22
2	8	T	C	C	C	C	C	C	C	C	Y		9676A75G01	292B319G22
2	8	T	C	C	C	C	C	C	C	C	P		9666A24G01	<1>
2	8	T	C	C	C	C	C	C	C	C	P		9689A34G01	<1>
2	8	T	R	R	R	R	R	R	R	R	T		716B562G28	292B319G22
2	8	T	T	5	5	R	R	8	8	7	7		9682A68G01	<1>
2	8	T	T	9	9	9	9	9	9	9	9		9669A40G01	<1>
2	8	T	T	C	C	C	C	C	C	C	C		1586C42G16	<1>
2	8	T	T	C	C	C	C	C	C	C	C		774B430G28	<1>
2	8	T	T	R	R	8	8	7	7	5	5		991A935G01	<1>
2	8	W	W	C	C	C	C	C	C	C	C		9666A51G01	<1>
2	8	Z	C	C	C	C	C	C	C	C	Z		9689A77G01	292B319G22
1	9	C	C	C	C	C	C	C	C	C	P		129A541G01	<1>
1	9	C	C	C	C	C	C	C	C	C	T		188A286G01	<1>
1	9	C	C	C	C	C	C	C	C	C	P		670B197G16	<1>
1	9	C	C	C	C	C	C	C	C	C	P		1586C42G40	<1>
1	9	C	C	C	C	C	C	C	C	C	T		1586C42G35	<1>
1	9	P	C	C	C	C	C	C	C	C	C		714B325G23	<1>
1	9	P	C	C	C	B	C	C	C	C	B		498A030G01	<1>

Poten-	Cur-	Arrangement										Style No.	In-Service
tials	rents	A	B	C	D	E	F	G	H	I	J		Test Plug
1	9	T	8 - 8	C - C	5 - 5	R - R	8					9688A48G01	<1>
0	10	5 - A	5 - A	5 - A	5 - A	5 - A	5 - A					9689A26G01	<1>
0	10	6 - 6	6 - 6	6 - 6	6 - 6	6 - 6	6 - 6					9664A94G01	<1>
0	10	8 - 8	8 - 8	8 - 8	8 - 8	8 - 8	8 - 8					9682A94G01	<1>
0	10	C	C	C	C	C	C	C	C	C	C	129A529G01	<1>
0	10	C	C	C	C	C	C	C	C	C	C	774B430G17	<1>
0	10	C	C	C	C - C	C - C	C - C	C - C	C			9676A18G01	<1>
0	10	C	C	C	C - C	C - C	C - C	C - C	C	C		9688A75G01	<1>
0	10	C	C - B	C	C - B	C	C - B	C				716B562G14	<1>
0	10	C	C - C	C - C	C - C	C - C	C - C	C - C	C			716B562G13	<1>
0	10	C - A	C - A	C - A	C - A	C - A	C - A	C - A				9689A03G01	<1>
0	10	C - C	5 - 5	R - R	8 - 8	8 - 8	8 - 8					9689A11G01	<1>
0	10	C - C	C - C	C	C	C	C - C	C - C				714B325G26	<1>
0	10	C - C	C - C	C - C	8 - 8	8 - 8	8 - 8					9682A92G01	<1>
0	10	C - C	C - C	C - C	C - C	C - C	8 - 8					9682A91G01	<1>
0	10	C - C	C - C	C - C	C - C	C - C	C	C				774B430G15	<1>
0	10	C - C	C - C	C - C	C - C	C - C	C - C					498A020G01	<1>
0	10	C - C	C - C	C - C	C - C	C - C	R	R				9676A23G01	<1>
0	10	C - C	C - C	C - C	C - C	C - C	C - C					9676A20G01	<1>
0	10	C - C - C - A	C - A	C - A	C - A	C - A						9683A92G01	<1>
0	10	C - C - C - A	C - C	C - C	C - A							774B430G14	<1>
0	10	C - C - C - A	C - C	C - C	C - A	C - C						1586C42G02	<1>
0	10	C - C - C - B	C - C	C - C	C - C	C - B						498A001G01	<1>
0	10	C - C - C - C	C - C	C - C	C - C	C - C						714B325G14	<1>
0	10	C - C - C - C	C - C	C - C	C - C	C - C						9666A40G01	<1>
0	10	C - C - C - C	C - C	C - C	C - C	C - C						774B430G23	<1>
0	10	C - C - C - C	C - C	C - C	C - C	R - R						9666A41G01	<1>
0	10	C - D	C - D	C - D	C - D	C - D						9676A07G01	<1>
0	10	C - E	C - E	C - E	C - E	C - E						714B325G09	<1>
0	10	J	J	J	J	J	J	J	J	J	J	291B962G31	<1>
0	10	R	R	R	R	R	R	R	R	R	R	9682A54G01	<1>
0	10	R - 6 - 7 - C	R - 6 - 7 - C	8 - C								9689A43G01	<1>
0	10	R - A	R - A	R - A	R - A	R - A						9689A17G01	<1>
0	10	R - B	R - B	R - B	R - B	R - B						714B325G10	<1>
0	10	R - C	R - C	R - C	R - C	R - C						716B562G09	<1>
0	10	R - R	6 - 6	7 - 7	8 - 8	C - C						9688A51G01	<1>
0	10	R - R	R - R	R - R	R - R	R - R						9663A33G01	<1>

Table 2. FT-1 switch selection by style

Potentials	Currents	Style No.	Code
10	0	129A501G01	001
8	0	129A502G01	002
7	0	129A503G01	003
6	0	129A504G01	004
5	0	129A505G01	005
4	0	129A506G01	006
2	2	129A507G01	007
3	2	129A508G01	008
4	2	129A509G01	009
5	2	129A510G01	010
3	4	129A511G01	011
4	4	129A512G01	012
6	4	129A513G01	013
4	6	129A514G01	014
3	6	129A515G01	015
0	6	129A516G01	016
0	8	129A517G01	017
2	8	129A518G01	018
2	8	129A519G01	019
6	4	129A520G01	020
2	6	129A521G01	021
0	6	129A523G01	022
4	0	129A524G01	023
2	6	129A525G01	024
7	0	129A526G01	025
4	6	129A528G01	026
0	10	129A529G01	027
4	4	129A530G01	028
0	2	129A531G01	029
6	4	129A532G01	030
3	2	129A533G01	031
2	0	129A534G01	032
3	7	129A535G01	033
8	0	129A536G01	331
2	4	129A537G01	034
4	0	129A538G01	035
10	0	129A539G01	036
1	6	129A540G01	332
1	9	129A541G01	037
8	2	129A542G01	038
3	3	129A543G01	039
4	4	129A544G01	040
5	4	129A545G01	041
8	0	129A546G01	042
7	0	129A547G01	043
9	0	129A548G01	044
8	0	129A549G01	045

Potentials	Currents	Style No.	Code
6	0	129A550G01	046
9	0	129A551G01	047
6	3	129A552G01	333
7	3	129A553G01	048
0	5	129A555G01	049
3	7	1485B70G09	175
3	7	1485B70G10	176
3	7	1485B70G11	177
4	0	1586C39G01	336
4	0	1586C39G02	203
6	0	1586C40G01	206
0	8	1586C41G01	278
0	10	1586C42G02	337
4	6	1586C42G03	288
4	6	1586C42G05	338
10	0	1586C42G06	317
2	8	1586C42G08	340
2	8	1586C42G09	188
4	6	1586C42G10	189
6	4	1586C42G11	190
6	4	1586C42G12	191
6	4	1586C42G13	192
6	4	1586C42G14	243
10	0	1586C42G15	242
2	8	1586C42G16	204
3	7	1586C42G17	205
4	6	1586C42G18	207
3	7	1586C42G19	208
8	2	1586C42G20	209
4	6	1586C42G21	210
6	4	1586C42G22	211
10	0	1586C42G23	212
10	0	1586C42G24	213
10	0	1586C42G25	214
8	2	1586C42G26	215
6	4	1586C42G27	217
10	0	1586C42G28	244
10	0	1586C42G29	245
10	0	1586C42G30	246
10	0	1586C42G31	247
8	2	1586C42G32	248
8	2	1586C42G33	249
4	6	1586C42G34	250
1	9	1586C42G35	251
4	6	1586C42G36	252
4	6	1586C42G37	253
8	2	1586C42G38	254

Potentials	Currents	Style No.	Code
9	1	1586C42G39	255
1	9	1586C42G40	257
10	0	1586C42G41	258
2	8	1586C42G42	259
3	7	1586C42G43	260
10	0	1586C42G44	261
10	0	1586C42G45	262
10	0	1586C42G46	263
8	2	1586C42G47	264
4	6	1586C42G48	265
0	8	188A229G01	050
5	2	188A261G01	051
1	9	188A286G01	280
0	6	188A304G01	052
6	0	188A416G01	053
0	6	188A454G01	054
4	3	188A477G01	055
4	6	188A523G01	056
3	4	188A618G01	057
5	2	188A622G01	341
6	2	188A632G01	058
5	4	188A633G01	059
0	2	291B954G12	088
2	0	291B954G13	089
2	0	291B954G14	342
2	0	291B954G15	343
2	0	291B954G16	090
0	4	291B956G13	091
2	2	291B956G18	092
0	4	291B956G23	093
4	0	291B956G24	344
4	0	291B956G25	345
3	1	291B956G26	346
0	4	291B956G27	195
1	3	291B956G28	347
0	4	291B956G29	094
2	2	291B956G30	095
4	0	291B956G31	193
4	0	291B956G32	196
3	2	291B957G09	348
5	0	291B957G15	096
3	2	291B957G16	349
3	2	291B957G17	350
3	3	291B958G24	351
6	0	291B958G25	216
0	6	291B958G26	352
2	4	291B958G27	353

Potentials	Currents	Style No.	Code
0	6	291B958G28	270
0	6	291B958G29	098
2	4	291B958G30	099
2	4	291B958G31	100
6	0	291B958G33	102
5	2	291B959G18	103
7	0	291B959G19	104
3	4	291B959G20	354
3	4	291B959G26	355
5	2	291B959G27	356
7	0	291B959G28	357
0	7	291B959G29	105
7	0	291B959G30	106
3	4	291B959G32	108
7	0	291B959G33	109
0	8	291B960G20	358
6	2	291B960G26	110
3	5	291B960G27	359
0	8	291B960G33	360
6	2	291B960G36	111
8	0	291B960G37	187
2	6	291B960G38	361
8	0	291B960G39	112
5	4	291B961G22	362
6	3	291B961G23	113
3	7	291B961G25	114
2	7	291B961G26	115
3	6	291B961G27	364
5	4	291B961G28	365
3	6	291B961G29	366
6	3	291B961G30	116
0	10	291B962G31	367
0	10	498A001G01	060
1	4	498A002G01	061
1	6	498A003G01	368
0	8	498A004G01	062
3	4	498A008G01	063
1	8	498A009G01	064
4	6	498A010G01	065
9	1	498A011G01	066
4	0	498A012G01	067
7	0	498A013G01	068
0	6	498A014G01	069
6	4	498A015G01	070
4	4	498A016G01	071
0	6	498A017G01	369
1	7	498A018G01	370
1	7	498A019G01	072
0	10	498A020G01	073
0	9	498A021G01	074
4	0	498A022G01	075
0	9	498A023G01	371
3	6	498A024G01	372
0	8	498A025G01	373
0	2	498A026G01	076
0	4	498A027G01	077

Potentials	Currents	Style No.	Code
4	5	498A028G01	374
0	8	498A029G01	375
1	9	498A030G01	078
2	8	498A031G01	376
2	8	498A032G01	079
4	4	629A315G01	080
6	3	629A483G01	081
6	0	629A568G01	377
6	4	629A735G01	378
1	9	670B197G16	117
8	2	670B197G17	118
4	6	670B197G18	119
6	4	670B197G19	379
5	5	670B197G20	120
10	0	670B197G21	380
3	7	670B197G22	121
4	6	670B197G23	122
10	0	670B197G24	123
6	4	670B197G25	124
10	0	670B197G26	185
4	6	670B197G27	125
6	4	670B197G28	126
10	0	670B197G31	127
4	6	670B197G32	128
8	2	670B197G33	178
6	4	670B197G34	179
3	7	670B197G35	180
10	0	670B197G36	181
6	4	670B197G37	182
2	8	670B197G38	200
0	10	714B325G09	129
0	10	714B325G10	130
3	7	714B325G11	381
2	8	714B325G12	382
2	8	714B325G13	383
0	10	714B325G14	384
2	8	714B325G15	131
6	4	714B325G16	132
4	6	714B325G17	133
6	4	714B325G18	134
4	6	714B325G19	385
4	6	714B325G20	386
2	8	714B325G21	387
3	7	714B325G22	388
1	9	714B325G23	389
4	6	714B325G24	390
3	7	714B325G25	135
0	10	714B325G26	391
6	4	714B325G27	392
6	4	714B325G28	393
6	4	714B325G29	394
8	2	714B325G30	136
8	2	714B325G31	395
4	6	714B325G32	137
0	10	716B562G09	139
10	0	716B562G10	140

Potentials	Currents	Style No.	Code
2	8	716B562G11	396
3	7	716B562G12	397
0	10	716B562G13	398
0	10	716B562G14	141
6	4	716B562G15	142
4	6	716B562G16	399
6	4	716B562G17	400
4	6	716B562G18	401
6	4	716B562G19	143
6	4	716B562G20	402
8	2	716B562G21	403
2	8	716B562G24	404
2	8	716B562G25	184
8	2	716B562G26	145
2	8	716B562G27	146
2	8	716B562G28	147
3	7	716B562G30	149
8	2	716B562G35	152
6	4	716B562G36	256
4	6	716B562G37	144
2	8	716B562G38	153
2	8	716B562G39	154
3	0	716B871G09	155
0	3	716B871G10	405
3	0	716B871G11	156
3	0	716B871G12	157
8	0	719B591G09	406
8	0	719B591G10	407
4	4	719B591G11	408
8	0	719B591G12	158
4	4	719B591G13	159
8	0	719B591G14	160
0	4	763A109G01	410
4	0	763A166G01	411
6	2	763A167G01	412
7	0	763A168G01	413
4	6	774B430G09	161
4	6	774B430G10	162
2	8	774B430G11	163
2	8	774B430G12	164
4	6	774B430G13	165
0	10	774B430G14	414
0	10	774B430G15	166
3	7	774B430G16	167
0	10	774B430G17	168
4	6	774B430G18	169
10	0	774B430G19	170
4	6	774B430G20	171
4	6	774B430G21	172
2	8	774B430G22	173
0	10	774B430G23	174
4	6	774B430G24	183
2	8	774B430G28	201
1	0	774B542G09	415
6	4	836A867G01	416
0	4	837A087G01	417

Potentials	Currents	Style No.	Code
0	8	837A098G01	418
0	8	837A099G01	419
2	8	837A101G01	082
2	8	837A407G01	083
2	8	837A616G01	186
2	8	837A664G01	420
8	2	837A665G01	202
6	0	837A889G01	421
6	4	849A307G01	422
2	8	849A513G01	084
3	6	861A551G01	423
6	4	861A670G01	085
4	0	862A584G01	086
2	8	876A157G01	425
6	4	877A077G01	087
10	0	9641A64G01	619
2	8	9642A36G01	618
10	0	9646A77G01	620
8	2	9647A11G01	627
8	2	9647A12G01	628
4	0	9647A17G01	629
2	8	9647A18G01	630
9	1	9647A19G01	631
4	6	9647A20G01	632
10	0	9647A21G01	633
10	0	9647A22G01	634
4	6	9647A23G01	635
8	2	9647A98G01	636
10	0	9649A37G01	637
4	6	9652A25G01	832
10	0	9652A26G01	833
10	0	9652A27G01	834
4	6	9652A28G01	835
10	0	9652A29G01	870
6	4	9652A30G01	871
0	8	9660A84G01	266
4	6	9660A85G01	267
6	4	9660A91G01	268
10	0	9660A92G01	269
4	6	9660A96G01	272
0	6	9660A97G01	273
10	0	9663A25G01	274
6	4	9663A31G01	275
0	10	9663A33G01	276
3	6	9663A34G01	277
10	0	9663A41G01	279
3	7	9663A59G01	281
8	2	9663A60G01	282
3	6	9663A74G01	283
1	6	9663A77G01	284
1	2	9663A78G01	285
7	0	9663A79G01	286
4	0	9663A80G01	287
10	0	9664A78G01	758
10	0	9664A79G01	759
4	6	9664A80G01	760

Potentials	Currents	Style No.	Code
4	6	9664A81G01	761
2	8	9664A82G01	762
2	8	9664A83G01	763
10	0	9664A84G01	764
4	6	9664A85G01	765
4	6	9664A86G01	766
4	6	9664A87G01	767
10	0	9664A88G01	768
4	6	9664A89G01	769
10	0	9664A92G01	770
4	6	9664A93G01	771
0	10	9664A94G01	772
10	0	9664A97G01	775
10	0	9664A98G01	776
0	4	9666A12G01	616
10	0	9666A13G01	617
4	6	9666A20G01	720
4	6	9666A21G01	721
2	8	9666A23G01	722
2	8	9666A24G01	723
2	8	9666A26G01	724
6	4	9666A27G01	725
8	2	9666A28G01	726
8	2	9666A34G01	777
2	8	9666A35G01	778
10	0	9666A36G01	779
6	4	9666A37G01	780
4	6	9666A38G01	781
6	0	9666A39G01	782
0	10	9666A40G01	783
0	10	9666A41G01	784
8	2	9666A42G01	785
10	0	9666A43G01	786
4	6	9666A44G01	787
10	0	9666A45G01	788
4	6	9666A46G01	789
10	0	9666A47G01	790
2	8	9666A48G01	791
10	0	9666A49G01	792
10	0	9666A50G01	793
2	8	9666A51G01	794
10	0	9666A52G01	795
10	0	9666A53G01	796
4	6	9666A54G01	797
4	6	9666A55G01	798
3	7	9666A56G01	799
10	0	9666A58G01	801
4	6	9666A59G01	802
4	6	9666A60G01	803
10	0	9666A61G01	804
10	0	9666A62G01	805
4	6	9666A63G01	806
2	8	9666A64G01	807
10	0	9666A65G01	808
4	6	9666A66G01	809
4	6	9666A67G01	810

Potentials	Currents	Style No.	Code
8	2	9666A69G01	811
4	6	9666A72G01	812
10	0	9666A73G01	813
10	0	9666A76G01	815
10	0	9666A77G01	816
0	8	9666A78G01	817
10	0	9666A79G01	818
10	0	9666A80G01	819
8	2	9666A82G01	820
0	6	9666A83G01	821
4	6	9666A84G01	822
0	8	9666A85G01	823
10	0	9666A86G01	824
10	0	9666A87G01	825
4	6	9666A88G01	826
3	7	9666A89G01	827
10	0	9666A90G01	828
4	6	9666A91G01	829
10	0	9666A92G01	831
10	0	9666A93G01	836
4	6	9666A94G01	837
3	2	9666A95G01	838
8	2	9666A96G01	839
6	4	9666A97G01	840
4	2	9667A02G01	289
10	0	9667A03G01	290
10	0	9667A06G01	291
5	2	9667A17G01	292
2	6	9667A21G01	293
4	6	9667A22G01	294
2	8	9667A68G01	295
4	6	9667A69G01	296
10	0	9667A78G01	297
4	6	9667A80G01	298
10	0	9667A86G01	299
10	0	9667A93G01	300
10	0	9668A27G01	301
10	0	9668A54G01	304
2	6	9668A69G01	305
1	8	9668A70G01	306
4	6	9669A30G01	915
6	0	9669A31G01	916
4	4	9669A32G01	917
10	0	9669A33G01	918
10	0	9669A34G01	919
2	8	9669A35G01	920
4	6	9669A36G01	921
10	0	9669A37G01	922
10	0	9669A38G01	923
10	0	9669A39G01	924
2	8	9669A40G01	925
10	0	9669A41G01	926
4	6	9669A42G01	927
4	6	9669A43G01	928
4	6	9670A05G01	307
10	0	9670A34G01	308

Potentials	Currents	Style No.	Code
10	0	9670A35G01	309
10	0	9670A97G01	310
10	0	9670A98G01	311
2	8	9671A04G01	312
2	2	9671A05G01	313
2	8	9671A12G01	314
10	0	9671A13G01	315
2	8	9671A22G01	316
3	7	9671A26G01	318
10	0	9671A68G01	319
10	0	9671A69G01	320
4	6	9671A70G01	321
4	6	9671A93G01	322
10	0	9671A94G01	323
10	0	9671A95G01	324
4	6	9672A01G01	325
10	0	9672A02G01	326
4	2	9672A03G01	327
0	8	9672A10G01	328
2	8	9672A23G01	329
10	0	9672A71G01	330
0	6	9672A72G01	426
4	0	9672A73G01	427
10	0	9672A74G01	428
10	0	9672A75G01	429
10	0	9672A77G01	430
6	4	9672A80G01	431
8	2	9672A83G01	432
3	7	9672A86G01	433
6	4	9672A87G01	434
2	8	9672A88G01	435
8	2	9672A89G01	436
4	6	9672A90G01	437
2	8	9672A94G01	438
2	8	9672A95G01	439
10	0	9672A97G01	440
10	0	9672A98G01	441
6	4	9672A99G01	442
2	8	9676A01G01	443
8	2	9676A04G01	444
6	4	9676A05G01	445
6	4	9676A06G01	446
0	10	9676A07G01	447
10	0	9676A08G01	448
6	4	9676A09G01	449
4	6	9676A10G01	450
2	8	9676A11G01	451
10	0	9676A14G01	452
8	2	9676A15G01	453
4	6	9676A17G01	454
0	10	9676A18G01	455
3	3	9676A19G01	456
0	10	9676A20G01	457
0	10	9676A23G01	458
0	7	9676A24G01	459
0	9	9676A25G01	460

Potentials	Currents	Style No.	Code
4	0	9676A26G01	461
4	0	9676A27G01	462
10	0	9676A34G01	463
4	6	9676A35G01	464
2	2	9676A36G01	465
5	0	9676A37G01	466
2	0	9676A38G01	467
10	0	9676A53G01	468
4	6	9676A55G01	469
4	6	9676A58G01	470
4	6	9676A60G01	471
6	0	9676A65G01	473
4	6	9676A68G01	474
6	4	9676A71G01	475
10	0	9676A72G01	476
10	0	9676A73G01	477
10	0	9676A74G01	478
2	8	9676A75G01	479
3	7	9676A76G01	480
3	4	9676A79G01	481
4	6	9676A80G01	482
10	0	9676A81G01	483
2	8	9676A83G01	484
10	0	9676A84G01	485
8	2	9676A86G01	486
10	0	9676A87G01	487
10	0	9676A88G01	488
10	0	9676A89G01	489
10	0	9676A90G01	490
10	0	9676A91G01	491
10	0	9676A93G01	492
10	0	9676A94G01	493
4	6	9676A95G01	494
2	8	9676A96G01	495
10	0	9676A97G01	496
4	6	9676A98G01	497
4	6	9676A99G01	498
10	0	9682A19G01	830
2	8	9682A24G01	841
8	2	9682A25G01	842
10	0	9682A29G01	846
10	0	9682A30G01	847
10	0	9682A31G01	848
10	0	9682A32G01	849
10	0	9682A35G01	850
6	4	9682A36G01	851
10	0	9682A37G01	852
10	0	9682A38G01	853
4	6	9682A39G01	854
10	0	9682A41G01	856
10	0	9682A42G01	857
2	5	9682A43G01	858
9	0	9682A44G01	859
10	0	9682A45G01	860
10	0	9682A46G01	861
2	8	9682A47G01	862

Potentials	Currents	Style No.	Code
4	6	9682A48G01	863
4	6	9682A49G01	864
4	6	9682A50G01	865
4	6	9682A51G01	866
10	0	9682A52G01	867
4	6	9682A53G01	868
0	10	9682A54G01	869
10	0	9682A57G01	874
10	0	9682A59G01	875
10	0	9682A60G01	876
2	8	9682A61G01	877
10	0	9682A62G01	878
10	0	9682A64G01	879
10	0	9682A65G01	880
10	0	9682A66G01	881
10	0	9682A67G01	882
2	8	9682A68G01	883
4	6	9682A69G01	884
10	0	9682A70G01	885
10	0	9682A71G01	886
10	0	9682A72G01	887
10	0	9682A73G01	888
8	2	9682A74G01	889
10	0	9682A76G01	891
10	0	9682A77G01	892
10	0	9682A78G01	893
10	0	9682A79G01	894
8	2	9682A80G01	895
4	6	9682A82G01	897
10	0	9682A83G01	898
4	6	9682A84G01	899
8	2	9682A85G01	900
4	6	9682A86G01	901
2	8	9682A87G01	902
10	0	9682A89G01	904
10	0	9682A90G01	905
0	10	9682A91G01	906
0	10	9682A92G01	907
4	6	9682A93G01	908
0	10	9682A94G01	909
10	0	9682A96G01	911
3	7	9682A97G01	912
6	4	9682A98G01	913
10	0	9682A99G01	914
10	0	9683A01G01	499
10	0	9683A02G01	500
10	0	9683A03G01	501
4	6	9683A04G01	502
4	6	9683A05G01	503
10	0	9683A06G01	504
4	6	9683A07G01	505
8	0	9683A10G01	507
4	6	9683A15G01	508
2	8	9683A16G01	509
10	0	9683A17G01	510
10	0	9683A18G01	511

Potentials	Currents	Style No.	Code
10	0	9683A19G01	512
4	6	9683A20G01	513
4	6	9683A21G01	514
2	6	9683A22G01	515
10	0	9683A61G01	549
10	0	9683A69G01	550
10	0	9683A70G01	551
6	2	9683A71G01	552
8	2	9683A72G01	553
4	6	9683A73G01	554
10	0	9683A75G01	555
0	6	9683A76G01	556
8	0	9683A80G01	557
6	0	9683A81G01	558
2	8	9683A87G01	559
10	0	9683A88G01	560
2	8	9683A89G01	561
0	10	9683A92G01	562
0	8	9683A93G01	563
6	4	9683A94G01	564
10	0	9683A95G01	565
3	7	9683A96G01	566
10	0	9683A97G01	567
4	6	9683A98G01	568
2	8	9683A99G01	569
4	6	9688A01G01	570
4	6	9688A02G01	571
2	2	9688A03G01	572
6	0	9688A04G01	573
8	2	9688A07G01	574
10	0	9688A08G01	575
10	0	9688A09G01	576
10	0	9688A10G01	577
4	6	9688A11G01	578
10	0	9688A12G01	579
10	0	9688A13G01	580
10	0	9688A14G01	581
10	0	9688A15G01	582
10	0	9688A16G01	583
10	0	9688A17G01	584
10	0	9688A18G01	585
10	0	9688A19G01	586
10	0	9688A20G01	587
4	6	9688A22G01	588
10	0	9688A23G01	589
10	0	9688A24G01	590
2	2	9688A25G01	591
10	0	9688A26G01	592
10	0	9688A28G01	594
0	6	9688A30G01	595
4	6	9688A38G01	596
6	0	9688A40G01	597
4	6	9688A41G01	598
0	8	9688A42G01	599
0	6	9688A43G01	600
10	0	9688A44G01	601

Potentials	Currents	Style No.	Code
9	0	9688A45G01	602
2	0	9688A46G01	603
1	9	9688A48G01	604
3	7	9688A50G01	605
0	10	9688A51G01	606
10	0	9688A52G01	607
10	0	9688A53G01	608
10	0	9688A54G01	609
5	0	9688A55G01	610
10	0	9688A56G01	611
10	0	9688A57G01	612
10	0	9688A58G01	613
10	0	9688A59G01	614
8	2	9688A62G01	615
3	0	9688A63G01	639
4	0	9688A64G01	640
2	6	9688A65G01	641
10	0	9688A66G01	642
3	1	9688A67G01	643
0	8	9688A70G01	644
10	0	9688A71G01	645
10	0	9688A72G01	646
10	0	9688A73G01	647
10	0	9688A74G01	648
0	10	9688A75G01	649
10	0	9688A76G01	650
10	0	9688A77G01	651
10	0	9688A78G01	652
4	0	9688A79G01	653
10	0	9688A80G01	654
10	0	9688A81G01	655
10	0	9688A82G01	656
3	4	9688A83G01	657
10	0	9688A84G01	658
2	8	9688A85G01	659
3	7	9688A86G01	660
4	6	9688A87G01	661
10	0	9688A88G01	662
10	0	9688A89G01	663
10	0	9688A90G01	664
2	8	9688A91G01	665
10	0	9688A92G01	666
10	0	9688A93G01	667
2	8	9688A94G01	668
10	0	9688A95G01	669
10	0	9688A96G01	670
8	2	9688A98G01	671
7	0	9688A99G01	672
6	4	9689A01G01	673
2	8	9689A02G01	674
0	10	9689A03G01	675
4	6	9689A04G01	676
4	6	9689A06G01	677
4	6	9689A07G01	678
10	0	9689A08G01	679
10	0	9689A09G01	680

Potentials	Currents	Style No.	Code
4	5	9689A10G01	681
0	10	9689A11G01	682
0	4	9689A12G01	683
10	0	9689A13G01	684
4	6	9689A14G01	685
10	0	9689A15G01	686
6	2	9689A16G01	687
0	10	9689A17G01	688
6	4	9689A18G01	689
4	6	9689A19G01	690
0	8	9689A20G01	691
9	0	9689A21G01	692
8	0	9689A22G01	693
0	6	9689A23G01	694
8	2	9689A25G01	695
0	10	9689A26G01	696
0	8	9689A27G01	697
4	6	9689A28G01	698
4	6	9689A29G01	699
10	0	9689A31G01	700
10	0	9689A32G01	701
4	6	9689A33G01	702
2	8	9689A34G01	703
10	0	9689A36G01	704
10	0	9689A37G01	705
6	4	9689A38G01	706
10	0	9689A40G01	707
4	6	9689A41G01	708
6	4	9689A42G01	709
0	10	9689A43G01	710
3	7	9689A45G01	711
10	0	9689A47G01	712
10	0	9689A49G01	713
10	0	9689A50G01	714
4	6	9689A53G01	716
1	4	9689A54G01	717
3	6	9689A56G01	718
3	6	9689A57G01	719
10	0	9689A59G01	727
10	0	9689A60G01	728
10	0	9689A61G01	729
10	0	9689A62G01	730
10	0	9689A63G01	731
10	0	9689A65G01	732
10	0	9689A69G01	734
10	0	9689A70G01	735
8	2	9689A72G01	736
6	4	9689A73G01	737
0	2	9689A74G01	738
3	0	9689A75G01	739
8	0	9689A76G01	740
2	8	9689A77G01	741
0	6	9689A78G01	742
10	0	9689A79G01	743
4	0	9689A80G01	744
6	4	9689A81G01	745

Potentials	Currents	Style No.	Code
4	6	9689A84G01	748
4	6	9689A85G01	749
8	2	9689A87G01	750
8	2	9689A88G01	751
4	6	9689A89G01	752
8	0	9689A90G01	753
10	0	9689A91G01	754
8	0	9689A95G01	755
10	0	9689A97G01	756
10	0	9689A99G01	757
6	4	991A218G01	218
1	3	991A219G01	219
10	0	991A220G01	220
10	0	991A221G01	221
10	0	991A222G01	222
10	0	991A223G01	223
10	0	991A224G01	224
10	0	991A225G01	225
8	2	991A226G01	226
10	0	991A227G01	227
10	0	991A228G01	228
10	0	991A229G01	229
10	0	991A230G01	230
6	4	991A231G01	231
10	0	991A232G01	232
2	8	991A233G01	233
4	6	991A234G01	234
6	4	991A235G01	235
4	6	991A236G01	236
2	8	991A237G01	237
4	6	991A238G01	238
4	6	991A239G01	239
4	6	991A240G01	240
8	2	991A241G01	241
10	0	991A302G01	302
10	0	991A303G01	303
6	4	991A334G01	334
6	4	991A335G01	335
6	4	991A506G01	506
10	0	991A621G01	621
6	4	991A622G01	622
10	0	991A623G01	623
4	6	991A624G01	624
2	8	991A625G01	625
0	4	991A626G01	626
10	0	991A814G01	814
10	0	991A929G01	929
10	0	991A930G01	930
10	0	991A931G01	931
4	0	991A932G01	932
8	2	991A933G01	933
8	2	991A934G01	934
2	8	991A935G01	935
1	6	991A936G01	936
8	0	991A937G01	937
2	6	991A938G01	938

Potentials	Currents	Style No.	Code
3	0	991A939G01	939
9	0	991A940G01	940
4	6	991A941G01	941
2	8	991A942G01	942
10	0	991A943G01	943
8	2	991A944G01	944

Table 3. FT-14 switch selection guide

Potentials	Currents	Arrangement	Style No.	Code
11 Pole		A B C D E F G H I J K L M N		
11	0	T T T T T T T T T T T . . .	FT4A11T11CN4004	4004
5	6	T T T C-C C-C C-C Y Y . . .	FT4A11T05CN4102	4102
3	8	C-C C-C C-C C-C T T T . . .	FT4A11T03CN4104	4104
3	8	C-C C-C C-C C-C Z Z Z . . .	FT4A11T03CN4006	4006
12 Pole		A B C D E F G H I J K L M N		
12	0	P P P P P P P P P P P P . .	FT4A12T12CN4007	4007
12	0	T T T T T T T T T T T T . .	FT4A12T12CN4008	4008
6	6	P P P P R-R R-R R-R Z Z . .	FT4A12T06CN4091	4091
4	8	. C-C C-C C-C C-C T T T T .	FT4A12T04CN4010	4010
4	8	C-C C-C C-C C-C T T P P . .	FT4A12T04CN4011	4011
4	8	C-C C-C C-C C-C Z Z Z Z . .	FT4A12T04CN4012	4012
4	8	P P P C-C C-C C-C C-C T . .	FT4A12T04CN4076	4076
4	8	T T T W . . C-C C-C C-C C-C	FT4A12T04CN4013	4013
0	12	C-C C-C C-C . C-C C-C C-C .	FT4A12T00CN4079	4079
0	12	C-C C-C C-C C-C C-C C-C . .	FT4A12T00CN4014	4014
13 Pole		A B C D E F G H I J K L M N		
13	0	T T T T T T T T T T T T T .	FT4A13T13CN4015	4015
9	4	P P P C-C P P P C-C P P P .	FT4A13T09CN4084	4084
0	13	C . C-5 C-5 C-5 C-5 C-5 C-5	FT4A13T00CN4088	4088
14 Pole		A B C D E F G H I J K L M N		
14	0	G G G G G G G G G G G G G G	FT4A14T14CN4083	4083
14	0	P P G Y Z Z T T T T T T T T	FT4A14T14CN4017	4017
14	0	P P P P P P P P P P P P P P	FT4A14T14CN4001	4001
14	0	P P P P T T T T T T T T T T	FT4A14T14CN4080	4080
14	0	T P T P T P T P T P T P T P	FT4A14T14CN4066	4066
14	0	T T T T P P P P P P P P P P	FT4A14T14CN4073	4073
14	0	T T T T T T T T T T T T T T	FT4A14T14CN4018	4018
14	0	T Y Z T T Y Y Z Z P P P Y Y	FT4A14T14CN4071	4071
14	0	W W W W W W W W W W W W W	FT4A14T14CN4090	4090
14	0	Y Y Y Y Y Y Y Y Y Y Y Y Y	FT4A14T14CN4078	4078
12	2	C-C P P P P P P T T T T T T	FT4A14T12CN4085	4085
10	4	T T T T T T T T P P C-C C-C	FT4A14T10CN4086	4086
8	6	C C C C C C P P P P T T T T	FT4A14T08CN4092	4092
8	6	C-C C-C C-C P P P P P P P P	FT4A14T08CN4067	4067
8	6	C-C C-C C-C P P P P T T T T	FT4A14T08CN4021	4021
8	6	C-C C-C C-C P P P T T T T T	FT4A14T08CN4077	4077
8	6	C-C C-C C-C T T T T P P P P	FT4A14T08CN4022	4022
8	6	C-C C-C C-C T T T T T T T T	FT4A14T08CN4023	4023
8	6	C-C C-C C-C T T T Y Y Y Y Y	FT4A14T08CN4024	4024
8	6	C-C C-C C-C T T Y Y Y Y Y Y	FT4A14T08CN4025	4025
8	6	C-C C-C C-C Z Z Z Y Y Y Y Y	FT4A14T08CN4026	4026
8	6	C-C C-C C-C Z Z Z T T Y Y Y	FT4A14T08CN4027	4027
8	6	C-C-C-C C-C P P P P T T T T	FT4A14T08CN4093	4093
8	6	P P P C-C C-C C-C P P P P P	FT4A14T08CN4003	4003
8	6	P P P C-C C-C C-C P T P P P	FT4A14T08CN4028	4028
8	6	T P O O P P P G C-C C-C C-C	FT4A14T08CN4101	4101

Potentials	Currents	Arrangement	Style No.	Code
8	6	T T C-C C-C C-C W W W W W W	FT4A14T08CN4097	4097
8	6	T T T C-C C-C C-C T T T T T	FT4A14T08CN4030	4030
8	6	T T T C-C C-C C-C W G O Y Z	FT4A14T08CN4031	4031
8	6	T T T T C-C C-C C-C T T T T	FT4A14T08CN4032	4032
8	6	T T T T T T T T C-C C-C C-C	FT4A14T08CN4099	4099
8	6	T Y Z R-R 6-6 7-7 P P P Y Y	FT4A14T08CN4072	4072
7	7	P P P P P P C-C C-C C-C C	FT4A14T07CN4033	4033
7	7	P P T T P P C-C C-C C-C C	FT4A14T07CN4034	4034
6	8	C-C C-C C-C C-C P P P P P P	FT4A14T06CN4068	4068
6	8	C-C C-C C-C C-C P P P P T T	FT4A14T06CN4035	4035
6	8	C-C C-C C-C C-C T T P P P P	FT4A14T06CN4036	4036
6	8	C-C C-C C-C C-C T T T T T T	FT4A14T06CN4037	4037
6	8	C-C C-C C-C C-C T Y Y Y Y Y	FT4A14T06CN4038	4038
6	8	C-C C-C C-C C-C Z O Y G P T	FT4A14T06CN4064	4064
6	8	C-C C-C C-C C-C Z Z Z Y Y Y	FT4A14T06CN4040	4040
6	8	P C-C C-C C-C C-C P P P P P	FT4A14T06CN4002	4002
6	8	P P O O O O R-R 6-6 7-7 8-8	FT4A14T06CN4043	4043
6	8	P P P C-C C-C C-C C-C P P P	FT4A14T06CN4044	4044
6	8	P P P P C-C C-C C-C C-C P P	FT4A14T06CN4065	4065
6	8	P P P P C-C C-C C-C C-C T T	FT4A14T06CN4045	4045
6	8	P P P P P P C-C C-C C-C C-C	FT4A14T06CN4046	4046
6	8	R-R R-R R-R R-R P P P P P P	FT4A14T06CN4095	4095
6	8	T C-C C-C C-C C-C P P P P P	FT4A14T06CN4103	4103
6	8	T C-C T C-C T C-C T C-C T T	FT4A14T06CN4048	4048
6	8	T P T O O O C-C C-C C-C 5-5	FT4A14T06CN4100	4100
6	8	T T C-C C-C C-C C-C W W W W	FT4A14T06CN4096	4096
6	8	T T T C-C C-C C-C 8-8 W P P	FT4A14T06CN4049	4049
6	8	T T T C-C C-C C-C C-C T T T	FT4A14T06CN4050	4050
6	8	T T T C-C C-C C-C T C-C T T	FT4A14T06CN4051	4051
6	8	T T T T C-C C-C C-C C-C T T	FT4A14T06CN4052	4052
6	8	T T T T T T C-C C-C C-C C-C	FT4A14T06CN4053	4053
6	8	T T T T Z Z C-C C-C C-C C-C	FT4A14T06CN4054	4054
6	8	T T T Z Z Z C-C C-C C-C C-C	FT4A14T06CN4055	4055
6	8	Z Z Z Z C-C C-C C-C C-C T T	FT4A14T06CN4074	4074
6	8	Z Z Z Z Z Z C-C C-C C-C C-C	FT4A14T06CN4056	4056
5	9	T P P P P C-C C-C C-C C-C C	FT4A14T05CN4057	4057
4	10	9-9 9-9 9-9 Z Z Z 9-9 9-9 Z	FT4A14T04CN4058	4058
4	10	C-C-C-C-C P T T T C-C-C-C-C	FT4A14T04CN4081	4081
4	10	C-R-5-6-C P P C-7-8-9-C P P	FT4A14T04CN4082	4082
4	10	P P C-C C-C C-C C-C C-C P P	FT4A14T04CN4059	4059
2	12	9-9 9-9 9-9 9-9 Z 9-9 9-9 Z	FT4A14T02CN4060	4060
2	12	C C C C C C C C C C C P P	FT4A14T02CN4094	4094
2	12	C-C C-C C-C C-C C-C C-C P P	FT4A14T02CN4098	4098
2	12	C-C C-C C-C C-C C-C C-C T T	FT4A14T02CN4061	4061
2	12	C-C-C-C C-C C-C C-C C-C P P	FT4A14T02CN4069	4069
2	12	P C-C C-C C-C C-C C-C C-C P	FT4A14T02CN4075	4075
2	12	T T C-C C-C C-C C-C C-C C-C	FT4A14T02CN4062	4062
0	14	C-5 C-5 C-5 C C-5 C-5 C-5 C	FT4A14T00CN4089	4089
0	14	C-5 C-5 C-5 C-5 C-5 C-5 C-5	FT4A14T00CN4087	4087
0	14	C-C C-C C-C C-C C-C C-C C-C	FT4A14T00CN4063	4063
0	14	C-C C-C C-C C-C C-C C-C C-C	FT4A14T00CN4070	4070

Notes

1. When a multi-position In-Service Test Plug is not available then the individual current circuit test plug can be used.
2. A standard FT-1 switch with screw termination will be supplied when using the Style Number per table 1. An optional FT-1 Switch with stud and nut terminals can be supplied at no additional charge when an “S” prefix is used with FT-1 switch style number (example: S129A501G01).
3. A standard FT-1 switch with black opaque cover will be supplied when using the style number per table 1. An optional FT-1 switch with clear cover can be supplied at no additional charge when a “C” prefix is used with FT-1 switch style number (Example: C129A501G01 or CS129A501G01 for clear cover and stud & nut terminals, per note 2).
4. FT-1 switch for FT-19R assembly application only will be supplied when using the prefix “R” or “RS” with the standard FT-1 switch style number on table 1.
5. A standard FT-14 switch with screw termination and clear cover will be supplied when using the style number per table 3.

For more information, please refer to FT Flexitest family descriptive bulletin DB 41-077 or visit us at www.ft1switch.com.

Additional notes

Additional notes

Contact us

ABB Inc.**Distribution Automation**

4300 Coral Ridge Drive

Coral Springs, Florida 33065

Telephone: +1 954-752-6700

Fax: +1 954-345-5329

www.abb.com/substationautomation

All sales are subject to ABB Inc.

General Terms and Conditions of Sale.

While every effort has been made to assure accuracy, the information in this document is subject to change without notice.

© Copyright 2010 ABB Inc. All rights reserved.

1VAC397062-SG Rev A August 2010